


FurseWELD

Cable to steel surface & pipe CS25 & CS27

Cable to steel surface & pipe CS25 - FurseWELD

	Stranded/solid circular conductor size A (mm ²)	Mould part no.	Order code	Powder cartridge part no.	Handle clamp part no.
	16 *	CS25-4-16	7TCA083910R2021	45P10	HCPK4
	25	CS25-4-25	7TCA083910R2024	45P10	HCPK4
	35	CS25-4-35	7TCA083910R2026	45P10	HCPK4
	50	CS25-4-50	7TCA083910R2027	65P10	HCPK4
	70	CS25-4-70	7TCA083910R2028	90P10	HCPK4
	95	CS25-4-95	7TCA083910R2032	115P10	HCPK4
	120	CS25-4-120	7TCA083910R2019	115P10	HCPK4
	150	CS25-4-150	7TCA083910R2020	150P10	HCPK4
	185	CS25-4-185	7TCA083910R2022	200P10	HCPK4
	240	CS25-4-240	7TCA083910R2023	200P10	HCPK4
	300	CS25-4-300	7TCA083910R2025	250P10	HCPK4

Special moulds for all FurseWELD products can be manufactured to meet specific customer applications on request

*1 x S103 Sleeve required when joining conductors 16 mm² or smaller


For order codes of powder cartridges and handle clamps, see pages 49-50

FurseWELD moulds should only be used with FurseWELD powders, handle clamps and accessories. If moulds, powders, handle clamps and accessories from other manufacturers are utilized, we cannot guarantee the safe use or the integrity of the completed joint

FurseWELD moulds for use with stranded conductor are designed for use with non-compacted conductor to BS EN 60228. If a mould for compacted conductor is required, please contact your local representative

Conductors must be installed in the orientation shown to achieve the correct connection

Cable to steel surface & pipe CS27 - FurseWELD

	Stranded/solid circular conductor size A (mm ²)	Mould part no.	Order code	Powder cartridge part no.	Handle clamp part no.
	16 *	CS27-4-16	7TCA083910R2041	45P10	HCPK4
	25	CS27-4-25	7TCA083910R2419	45P10	HCPK4
	35	CS27-4-35	7TCA083910R2042	45P10	HCPK4
	50	CS27-4-50	7TCA083910R2043	65P10	HCPK4
	70	CS27-4-70	7TCA083910R2044	115P10	HCPK4
	95	CS27-4-95	7TCA083910R2045	150P10	HCPK4
	120	CS27-4-120	7TCA083910R2272	150P10	HCPK4
	150	CS27-5-150	7TCA083910R3015	200P10	HCPK5
	185	CS27-5-185	7TCA083910R3016	250P10	HCPK5
	240	CS27-5-240	7TCA083910R2046	2 x 150P10	HCPK5
	300	CS27-5-300	7TCA083910R3017	2 x 200P10	HCPK5

Special moulds for all FurseWELD products can be manufactured to meet specific customer applications on request

*2 x S103 Sleeve required when joining conductors 16 mm² or smaller

For order codes of powder cartridges and handle clamps, see pages 49-50

FurseWELD moulds should only be used with FurseWELD powders, handle clamps and accessories. If moulds, powders, handle clamps and accessories from other manufacturers are utilized, we cannot guarantee the safe use or the integrity of the completed joint

FurseWELD moulds for use with stranded conductor are designed for use with non-compacted conductor to BS EN 60228. If a mould for compacted conductor is required, please contact your local representative

Conductors must be installed in the orientation shown to achieve the correct connection