# Security Technology Magnet Reed Contact Set MRS Technical Data



### Application

Reed contacts monitor the opening of windows and doors.

### Mode of operation

The reed contact is magnetically operated ba a separate permanent magnet. The two units are mounted in parallel (for surface mounting) or end (for drilling) at a maximum distance of 10 mm apart.

If the distance between them is increased, the reed contact opens, thereby interrupting the zone.

#### Design

The set consist 1 magnet, 1 reed contact with 4.0 m connection cable LIYY 4 x 0.14 mm<sup>2</sup>, 2 surface mount housing, 4 spacer plates, 2 flanges and 4 fixing screws (V4A antimagnetic).

The reed contact is encased in a circular housing and is thus protected against dust and damp.

The base plate is designed to hold the magnet or reed contact and enables 3 different cable outlets: lenthways, sideways and through the base of the plate for concealed wiring. Once the cap has been snapped into place, the fixing screws are also hidden.





# Magnet Reed contact Set MRS

#### Installation

The installation should in principle be carried out within the monitored area, i.e., inside. The reed contact is either screwed onto the fixed part of the window (or door) together with the housing or drilled in place without the housing. The magnet is attached to the movable part of the window in the same way.

During installation, the reed contact is drilled into the frame and the magnet is drilled into the window casement. Prior the insertion, the reed contact or the magnet is bonded to the flanges with cyanacrylat quick-drying adhesive. After insertion, the glued flanges are locked in position using V4A fixing screws. It should be ensured that the reed contact and magnet are placed vertically on the top of each other for drilling and that the supplied screws and spacer plates are used when screw mounting onto steel doors.

#### Installation examples



### **Technical Data**

#### Reed contact

Connection cable	4.0 m, 4 x 0.14 mm² ZGL
Soldering lugs	0.55 x 7 mm
Max. switching resistance	150 m $\Omega$
Max. switching voltage	60 V DC
Max. switching current	0.1 A
Max. switching capacity	5 VA
Contact material	Rhodium
Number of ampere turns	10 15 Aw
Temperature range	– 20 °C bis + 75 °C
Effective distance	
sideways:	max. 15 mm
end to end:	max. 15 mm
VdS approval (Class B)	G 198 531

Magnet	
Material	DYM
Dimensions	19 x 6 mm Ø
Housing	
Material	Polyamid
Resistant to temperature up to	100 °C
Colour white	RAL 9016
Colour brown	RAL 8017

# Magnet Reed contact Set MRS

### Wiring diagram



The configuration of the wires in the contact always guarantees that 2 adjacent wires can be connected to the control unit and the other two wires can be connected to the next detector or the EOL resistor. It is not necessary to measure the diameter of the cores.

### **Dimensions in mm**



### **Ordering Information**

Product photo	Description	Short	Order No.	bbn	Price	Weight	Pack
		designation		40 16779	group	1 pcs	unit
				EAN		kg	pcs.
	Reed Contact Set,	MRS/W	GH Q320 1972 R0001	50660 1	P4	0.06	1
	white						
( 1, 0	VdS No. G 198 531						
1000	Reed Contact Set,	MRS/B	GH Q320 1972 R0002	50659 5	P4	0.06	1
	brown						
× ×	VdS No. G 198 531						
	Saver Set, 20 Pcs.,	VMRS/W	GH Q320 1972 R0011	50658 8	P4	1.05	1
	white						
	Saver Set, 20 Pcs.,	VMRS/B	GH Q320 1972 R0012	50657 1	P4	1.05	1
	brown						

# Contact

### ABB STOTZ-KONTAKT GmbH

Eppelheimer Straße 82 69123 Heidelberg, Germany Phone: +49 (0)6221 701 607 Fax: +49 (0)6221 701 724 E-Mail: knx.marketing@de.abb.com

### Further Information and Local Contacts: www.abb.com/knx

### Note:

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail.

ABB AG does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents - in whole or in parts - is forbidden without prior written consent of ABB AG.

Copyright© 2011 ABB All rights reserved

