


We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden.  
© ABB '19

On-load tap-changer type UCGL./III, VUCGL./III, UCLL./III, VUCLL./III, UCCL./III, 19 tap positions, linear switching.  
Max. effective No. of turns in pos. 1.  
The tap-changer is delivered set in pos. 10, the preceding pos. was 9.

Lindningskopplare typ UCGL./III, VUCGL./III, UCLL./III, VUCLL./III, UCCL./III, 19 lägen, linjär koppling.  
Max. antal effektiva varv i läge 1.  
Lindningskopplaren levereras inställd i läge 10, föregående läge var 9.



Pos. Läge	Tap selector and diverter switch connect  Väljaren och lastkopplaren förbinder	
1	1-V-x	30
2	2-H-v	
3	3-V-x	
4	4-H-v	
5	5-V-x	
6	6-H-v	
7	7-V-x	
8	8-H-v	
9	9-V-x	
10	10-H-v	
11	11-V-x	
12	12-H-v	
13	13-V-x	
14	14-H-v	
15	15-V-x	
16	16-H-v	
17	17-V-x	
18	18-H-v	
19	19-V-x	

The tap-changer is shown in pos. 10, the preceding pos. was 9.  
The tap selector is seen from above.  
Contact arm V is located above contact arm H.

Lindningskopplaren visad i läge 10, föregående läge var 9.  
Väljaren sedd uppifrån.  
Kontaktarm V ligger över kontaktarm H.

Continuous lines show leads included in the tap-changer. Dashed lines show leads belonging to the cleats and leads.

Heldragna linjer visar ledare som ingår i lindningskopplaren. Streckade linjer visar ledare som tillhör anslutningsdonet.

1	VUCL added.	DAAN	21	32
Rev Ind	Revision	Appd	Year	Week

Accepted by qual control	Accepted for prod by	Description (English) CONNECTION DIAGRAM		DATAORIGINAL
Design checked by G.Andersson	Drawn by T.Larsen	Description (own language) KOPPLINGSSHEMA		File name 0367-15
Drawing checked by A.Hultberg	Issued by Dept Year Week COM/FOK 07 49	5492 0367-15		Lang 1
<b>ABB</b> Asea Brown Boveri				RevInd Cont -

Sheet	Cont
Year	Week
Dept	
RevInd	
Design checked by	
Drawn by	Form No.