
TECHNICAL DATA SHEET - INTERACTIVE PDF

Sleeve coupling, PVC

Without internal stop

Carlton[®]



Long-line sleeve coupling for use with schedule 40 and 80 conduit, telephone ducts, or power and communications

3-Part Specification: 25 06 33.51
End User Tools

Features:

- Available in 4" - 18" cut lengths
- Available in 2 ¼" - 7 ¼" diameters
- Non-metallic (PVC) with no internal stop
- P&C couplings can be concrete encased or buried

Applications:

- Can be used for repair work on existing systems

Conforms to:

- NEMA

Material / Finishes:

- PVC / Gray

PVC Sleeve couplings

Product selection						
Part no.	Conduit size	Conduit Type	A	B inch (mm)	C inch (mm)	
E200J	2"	P&C	4"	2.39 (60.7)	2.54 (64.5)	
E200JGT	2"	P&C	8"	2.39 (60.7)	2.54 (64.5)	
E200L	3"	P&C	6.5"	3.52 (89.4)	3.73 (94.7)	
E200M	3 ½"	P&C	6"	4.01 (101.9)	4.50 (114.3)	
E200N	4"	P&C	6"	4.52 (114.8)	4.79 (121.7)	
E200P	5"	P&C	6"	5.58 (141.7)	5.92 (150.4)	
E200R	6"	P&C	6"	6.65 (168.9)	7.04 (178.8)	
E600N	4"	P&C	10"	4.52 (114.8)	4.79 (121.7)	
E900DN	4"	Telephone	6"	4.37 (111.0)	4.67 (118.5)	
E900N	4"	Telephone	6"	4.37 (111.0)	4.67 (118.5)	
E900N18	4"	Telephone	18"	4.37 (111.0)	4.67 (118.5)	
E900NU	4"	Telephone	12"	4.37 (111.0)	4.67 (118.5)	
E900NW	4"	Telephone	6"	4.37 (111.0)	4.67 (118.5)	
E948H	1 ½"	Schedule 40 & 80	4"	1.92 (48.8)	2.23 (56.6)	
E948J	2"	Schedule 40 & 80	3"	2.39 (60.7)	2.72 (69.1)	
E948JR	2"	Schedule 40 & 80	6"	2.39 (60.7)	2.72 (69.1)	
E948K	2 ½"	Schedule 40 & 80	6"	2.89 (73.4)	3.11 (79.0)	
E948L	3"	Schedule 40 & 80	4"	3.52 (89.4)	3.98 (101.1)	
E948L6	3"	Schedule 40 & 80	6"	3.52 (89.4)	3.98 (101.1)	
E948N	4"	Schedule 40 & 80	6.5"	4.52 (114.8)	5.02 (127.5)	
E948N7	4"	Schedule 40 & 80	7"	4.52 (114.8)	5.02 (127.5)	
E948P	5"	Schedule 40 & 80	7"	5.58 (141.7)	6.13 (155.7)	
E948R	6"	Schedule 40 & 80	6"	6.65 (168.9)	7.23 (183.9)	
E948R10	6"	Schedule 40 & 80	10"	6.65 (168.9)	7.23 (183.9)	
E948R12	6"	Schedule 40 & 80	12"	6.65 (168.9)	7.23 (183.9)	

Note: Product must be installed in accordance with applicable national and local electrical codes.

