

FurseWELD

Bar to earth rod BR2

Bar to earth rod BR2 - FurseWELD

	Earth rod A ø (mm)	Earth rod B ø (")	Flat tape conductor size C (mm)	Mould part no.	Order code	Powder cartridge part no.	Handle clamp part no.
	14.2	5/8	25 x 3	BR2-4-142253	7TCA083910R0424	90P10	HCPK4
	14.2	5/8	25 x 4	BR2-4-142254	7TCA083910R0426	115P10	HCPK4
	14.2	5/8	25 x 6	BR2-4-142256	7TCA083910R0428	150P10	HCPK4
	14.2	5/8	30 x 2	BR2-4-142302	7TCA083910R0429	90P10	HCPK4
	14.2	5/8	30 x 3	BR2-4-142303	7TCA083910R0430	115P10	HCPK4
	14.2	5/8	30 x 4	BR2-4-142304	7TCA083910R0431	150P10	HCPK4
	14.2	5/8	30 x 5	BR2-4-142305	7TCA083910R0432	150P10	HCPK4
	14.2	5/8	38 x 5	BR2-4-142385	7TCA083910R0434	150P10	HCPK4
	14.2	5/8	38 x 6	BR2-4-142386	7TCA083910R0435	200P10	HCPK4
	14.2	5/8	40 x 3	BR2-4-142403	7TCA083910R0436	150P10	HCPK4
	14.2	5/8	40 x 4	BR2-4-142404	7TCA083910R0437	150P10	HCPK4
	14.2	5/8	40 x 5	BR2-4-142405	7TCA083910R0438	150P10	HCPK4
	14.2	5/8	40 x 6	BR2-4-142406	7TCA083910R0439	200P10	HCPK4
	14.2	5/8	50 x 3	BR2-4-142503	7TCA083910R0440	200P10	HCPK4
	14.2	5/8	50 x 4	BR2-4-142504	7TCA083910R0441	200P10	HCPK4
	14.2	5/8	50 x 5	BR2-4-142505	7TCA083910R0442	200P10	HCPK4
14.2	5/8	50 x 6	BR2-4-142506	7TCA083910R0443	250P10	HCPK4	

Suitable for connections to copperbond rods - for connections to solid copper and stainless steel rods please contact our sales office

Threaded portion of copperbond rods must be removed prior to welding

Special moulds for all FurseWELD products can be manufactured to meet specific customer applications on request

For order codes of powder cartridges and handle clamps, see pages 49-50

FurseWELD moulds should only be used with FurseWELD powders, handle clamps and accessories. If moulds, powders, handle clamps and accessories from other manufacturers are utilized, we cannot guarantee the safe use or the integrity of the completed joint

Conductors must be installed in the orientation shown to achieve the correct connection

FurseWELD

Bar to earth rod BR2

Bar to earth rod BR2 (continued) - FurseWELD

	Earth rod A ø (mm)	Earth rod B ø (")	Flat tape conductor size C (mm)	Mould part no.	Order code	Powder cartridge part no.	Handle clamp part no.
	17.2	3/4	25 x 3	BR2-4-172253	7TCA083910R0449	150P10	HCPK4
	17.2	3/4	25 x 4	BR2-4-172254	7TCA083910R0450	200P10	HCPK4
	17.2	3/4	25 x 6	BR2-4-172256	7TCA083910R0451	200P10	HCPK4
	17.2	3/4	30 x 2	BR2-4-172302	7TCA083910R0452	150P10	HCPK4
	17.2	3/4	30 x 3	BR2-4-172303	7TCA083910R0453	150P10	HCPK4
	17.2	3/4	30 x 4	BR2-4-172304	7TCA083910R0454	250P10	HCPK4
	17.2	3/4	30 x 5	BR2-4-172305	7TCA083910R2932	200P10	HCPK4
	17.2	3/4	38 x 5	BR2-4-172385	7TCA083910R0455	200P10	HCPK4
	17.2	3/4	38 x 6	BR2-4-172386	7TCA083910R0456	250P10	HCPK4
	17.2	3/4	40 x 3	BR2-4-172403	7TCA083910R0457	200P10	HCPK4
	17.2	3/4	40 x 4	BR2-4-172404	7TCA083910R0458	200P10	HCPK4
	17.2	3/4	40 x 5	BR2-4-172405	7TCA083910R0459	200P10	HCPK4
	17.2	3/4	40 x 6	BR2-4-172406	7TCA083910R2538	200P10	HCPK4
		17.2	3/4	50 x 3	BR2-5-172503	7TCA083910R2933	2 x 150P10
17.2		3/4	50 x 4	BR2-5-172504	7TCA083910R0462	2 x 150P10	HCPK5
17.2		3/4	50 x 5	BR2-5-172505	7TCA083910R0463	2 x 150P10	HCPK5
17.2		3/4	50 x 6	BR2-5-172506	7TCA083910R0464	2 x 150P10	HCPK5

Suitable for connections to copperbond rods - for connections to solid copper and stainless steel rods please contact our sales office

Threaded portion of copperbond rods must be removed prior to welding

Special moulds for all FurseWELD products can be manufactured to meet specific customer applications on request

For order codes of powder cartridges and handle clamps, see pages 49-50

FurseWELD moulds should only be used with FurseWELD powders, handle clamps and accessories. If moulds, powders, handle clamps and accessories from other manufacturers are utilized, we cannot guarantee the safe use or the integrity of the completed joint

Conductors must be installed in the orientation shown to achieve the correct connection