



MVI Fault Interrupter	E Slow - Relay	30-900 Ampere
MINIMUM TRIPPING AND TOTAL CLEARING TIME-CURRENT CHARACTERISTIC CURVES		
<p>Notes:</p> <ol style="list-style-type: none"> 1. Tested per C37.60 2. Accuracy is equal to +/- 10% of the current or time which ever is greater. 3. Minimum power up current: 15 Amperes 4. Curves are applicable to the operating range of -40°C to +65°C. 	<ol style="list-style-type: none"> 5. CT current sensing capability range: 10 -10,000 amperes RMS 6. Curves and trips are set using a personal computer or a control panel 7. The total clearing time-current characteristics curves represent the total time required to detect and interrupt the fault current 8. This curve in its entirety, including the title block, should be printed on a 11"x 17" sheet in order to conform with the C37.41 curve presentation standard (5.6 cm/decade). 	<p>E Slow Relay 30-900 Ampere</p>
	 497 Schooley's Mountain Road Hackettstown NJ, 07840	<p>Issue Date: December 13, 2022 Reference number: MVI-TCC-01</p>