


$V_{CE} = 4500\text{ V}$

$I_C = 800\text{ A}$



# ABB HiPak

## IGBT Module

# 5SNE 0800G450300

Doc. No. 5SYA15-00 2017-04-11

- Ultra low-loss, rugged SPT+ chip-set
- Smooth switching SPT+ chip-set for good EMC
- Industry standard package
- High power density
- AISiC base-plate for high power cycling capability
- AlN substrate for low thermal resistance
- Improved high reliability package
- Recognized under UL1557, File E196689



### Maximum rated values <sup>1)</sup>

Parameter	Symbol	Conditions	min	max	Unit
Collector-emitter voltage	$V_{CES}$	$V_{GE} = 0\text{ V}$		4500	V
DC collector current	$I_C$	$T_c = 85\text{ °C}$		800	A
Peak collector current	$I_{CM}$	$t_p = 1\text{ ms}, T_c = 85\text{ °C}$		1600	A
Gate-emitter voltage	$V_{GES}$		-20	20	V
Total power dissipation	$P_{tot}$	$T_c = 25\text{ °C}$ , per switch (IGBT)		7200	W
DC forward current	$I_F$			800	A
Peak forward current	$I_{FRM}$			1600	A
Surge current	$I_{FSM}$	$V_R = 0\text{ V}, T_{vj} = 125\text{ °C}$ , $t_p = 10\text{ ms}$ , half-sinewave		6000	A
IGBT short circuit SOA	$t_{psc}$	$V_{CC} = 3400\text{ V}, V_{CEMCHIP} \leq 4500\text{ V}$ $V_{GE} \leq 15\text{ V}, T_{vj} \leq 125\text{ °C}$		10	$\mu\text{s}$
Isolation voltage	$V_{isol}$	1 min, $f = 50\text{ Hz}$		10200	V
Junction temperature	$T_{vj}$			150	$^{\circ}\text{C}$
Junction operating temperature	$T_{vj(op)}$		-50	125	$^{\circ}\text{C}$
Case temperature	$T_c$		-50	125	$^{\circ}\text{C}$
Storage temperature	$T_{stg}$		-50	125	$^{\circ}\text{C}$
Mounting torques <sup>2)</sup>	$M_s$	Base- heatsink, M6 screws	4	6	Nm
	$M_{t1}$	Main terminals, M8 screws	8	10	
	$M_{t2}$	Auxiliary terminals, M4 screws	2	3	

<sup>1)</sup> Maximum rated values indicate limits beyond which damage to the device may occur per IEC 60747

<sup>2)</sup> For detailed mounting instructions refer to ABB Document No. 5SYA2039

ABB Switzerland Ltd, Semiconductors reserves the right to change specifications without notice.



IGBT characteristic values <sup>3)</sup>

Parameter	Symbol	Conditions	min	typ	max	Unit
Collector (-emitter) breakdown voltage	$V_{(BR)CES}$	$V_{GE} = 0 \text{ V}$ , $I_C = 10 \text{ mA}$ , $T_{vj} = 25 \text{ }^\circ\text{C}$	4500			V
Collector-emitter <sup>4)</sup> saturation voltage	$V_{CE \text{ sat}}$	$I_C = 800 \text{ A}$ , $V_{GE} = 15 \text{ V}$	$T_{vj} = 25 \text{ }^\circ\text{C}$	2.6	2.9	V
			$T_{vj} = 125 \text{ }^\circ\text{C}$	3.55	3.9	V
Collector cut-off current	$I_{CES}$	$V_{CE} = 4500 \text{ V}$ , $V_{GE} = 0 \text{ V}$	$T_{vj} = 25 \text{ }^\circ\text{C}$		8	mA
			$T_{vj} = 125 \text{ }^\circ\text{C}$		80	mA
Gate leakage current	$I_{GES}$	$V_{CE} = 0 \text{ V}$ , $V_{GE} = \pm 20 \text{ V}$ , $T_{vj} = 125 \text{ }^\circ\text{C}$	-500		500	nA
Gate-emitter threshold voltage	$V_{GE(TO)}$	$I_C = 160 \text{ mA}$ , $V_{CE} = V_{GE}$ , $T_{vj} = 25 \text{ }^\circ\text{C}$	4.5		6.5	V
Gate charge	$Q_{ge}$	$I_C = 800 \text{ A}$ , $V_{CE} = 2800 \text{ V}$ , $V_{GE} = -15 \text{ V} \dots 15 \text{ V}$		5.91		$\mu\text{C}$
Input capacitance	$C_{ies}$	$V_{CE} = 25 \text{ V}$ , $V_{GE} = 0 \text{ V}$ , $f = 1 \text{ MHz}$ , $T_{vj} = 25 \text{ }^\circ\text{C}$		80		nF
Output capacitance	$C_{oes}$			4.01		
Reverse transfer capacitance	$C_{res}$			1.72		
Internal gate resistance	$R_{Gint}$			1.75		$\Omega$
Turn-on delay time	$t_{d(on)}$	$V_{CC} = 2800 \text{ V}$ , $I_C = 800 \text{ A}$ , $R_G = 2.2 \text{ } \Omega$ , $C_{GE} = 150 \text{ nF}$ , $V_{GE} = \pm 15 \text{ V}$ , $L_S = 150 \text{ nH}$ , inductive load	$T_{vj} = 25 \text{ }^\circ\text{C}$	870		ns
			$T_{vj} = 125 \text{ }^\circ\text{C}$	860		
Rise time	$t_r$	$V_{CC} = 2800 \text{ V}$ , $I_C = 800 \text{ A}$ , $R_G = 2.2 \text{ } \Omega$ , $C_{GE} = 150 \text{ nF}$ , $V_{GE} = \pm 15 \text{ V}$ , $L_S = 150 \text{ nH}$ , inductive load	$T_{vj} = 25 \text{ }^\circ\text{C}$	150		ns
			$T_{vj} = 125 \text{ }^\circ\text{C}$	170		
Turn-off delay time	$t_{d(off)}$	$V_{CC} = 2800 \text{ V}$ , $I_C = 800 \text{ A}$ , $R_G = 2.2 \text{ } \Omega$ , $C_{GE} = 150 \text{ nF}$ , $V_{GE} = \pm 15 \text{ V}$ , $L_S = 150 \text{ nH}$ , inductive load	$T_{vj} = 25 \text{ }^\circ\text{C}$	2070		ns
			$T_{vj} = 125 \text{ }^\circ\text{C}$	2220		
Fall time	$t_f$	$V_{CC} = 2800 \text{ V}$ , $I_C = 800 \text{ A}$ , $R_G = 2.2 \text{ } \Omega$ , $C_{GE} = 150 \text{ nF}$ , $V_{GE} = \pm 15 \text{ V}$ , $L_S = 150 \text{ nH}$ , inductive load	$T_{vj} = 25 \text{ }^\circ\text{C}$	510		ns
			$T_{vj} = 125 \text{ }^\circ\text{C}$	600		
Turn-on switching energy	$E_{on}$	$V_{CC} = 2800 \text{ V}$ , $I_C = 800 \text{ A}$ , $R_G = 2.2 \text{ } \Omega$ , $C_{GE} = 150 \text{ nF}$ , $V_{GE} = \pm 15 \text{ V}$ , $L_S = 150 \text{ nH}$ , inductive load	$T_{vj} = 25 \text{ }^\circ\text{C}$	1850		mJ
			$T_{vj} = 125 \text{ }^\circ\text{C}$	2580		
Turn-off switching energy	$E_{off}$	$V_{CC} = 2800 \text{ V}$ , $I_C = 800 \text{ A}$ , $R_G = 2.2 \text{ } \Omega$ , $C_{GE} = 150 \text{ nF}$ , $V_{GE} = \pm 15 \text{ V}$ , $L_S = 150 \text{ nH}$ , inductive load	$T_{vj} = 25 \text{ }^\circ\text{C}$	3150		mJ
			$T_{vj} = 125 \text{ }^\circ\text{C}$	3780		
Short circuit current	$I_{SC}$	$t_{psc} \leq 10 \text{ } \mu\text{s}$ , $V_{GE} = 15 \text{ V}$ , $T_{vj} = 125 \text{ }^\circ\text{C}$ , $V_{CC} = 3400 \text{ V}$ , $V_{CEM \text{ CHIP}} \leq 4500 \text{ V}$		3500		A
Module stray inductance	$L_S \text{ CE}$			27		nH
Resistance, terminal-chip	$R_{CC'+EE'}$		$T_C = 25 \text{ }^\circ\text{C}$	0.11		m $\Omega$
			$T_C = 125 \text{ }^\circ\text{C}$	0.15		

<sup>3)</sup> Characteristic values according to IEC 60747 – 9<sup>4)</sup> Collector-emitter saturation voltage is given at chip level

**Diode characteristic values** <sup>5)</sup>

Parameter	Symbol	Conditions	min	typ	max	Unit
Forward voltage <sup>6)</sup>	$V_F$	$I_F = 800 \text{ A}$	$T_{vj} = 25 \text{ }^\circ\text{C}$	3.2	3.7	V
			$T_{vj} = 125 \text{ }^\circ\text{C}$	3.5	4	
Reverse recovery current	$I_{rr}$	$V_{CC} = 2800 \text{ V},$ $I_F = 800 \text{ A},$	$T_{vj} = 25 \text{ }^\circ\text{C}$	1110		A
			$T_{vj} = 125 \text{ }^\circ\text{C}$	1180		
Recovered charge	$Q_{rr}$	$V_{GE} = \pm 15 \text{ V},$ $R_G = 2.2 \text{ } \Omega,$	$T_{vj} = 25 \text{ }^\circ\text{C}$	730		$\mu\text{C}$
			$T_{vj} = 125 \text{ }^\circ\text{C}$	1120		
Reverse recovery time	$t_{rr}$	$C_{GE} = 150 \text{ nF},$ $L_s = 150 \text{ nH}$ inductive load	$T_{vj} = 25 \text{ }^\circ\text{C}$	1150		ns
			$T_{vj} = 125 \text{ }^\circ\text{C}$	1650		
Reverse recovery energy	$E_{rec}$		$T_{vj} = 25 \text{ }^\circ\text{C}$	1140		mJ
			$T_{vj} = 125 \text{ }^\circ\text{C}$	1880		

<sup>5)</sup> Characteristic values according to IEC 60747 – 2

<sup>6)</sup> Forward voltage is given at chip level

**Package properties** <sup>7)</sup>

Parameter	Symbol	Conditions	min	typ	max	Unit
IGBT thermal resistance junction to case	$R_{th(j-c)IGBT}$				0.014	K/W
Diode thermal resistance junction to case	$R_{th(j-c)DIODE}$				0.028	K/W
IGBT thermal resistance <sup>2)</sup> case to heatsink	$R_{th(c-s)IGBT}$	IGBT per switch, I grease = $1\text{W/m} \times \text{K}$		0.013		K/W
Diode thermal resistance <sup>7)</sup> case to heatsink	$R_{th(c-s)DIODE}$	Diode per switch, I grease = $1\text{W/m} \times \text{K}$		0.027		K/W
Partial discharge extinction voltage	$V_e$	$f = 50 \text{ Hz}, Q_{PD} \leq 10\text{pC}$ (acc. to IEC 61287)	5100			V
Comparative tracking index	CTI			<sup>3</sup> 600		


<sup>2)</sup> For detailed mounting instructions refer to ABB Document No. 5SYA2039

**Mechanical properties** <sup>7)</sup>


Parameter	Symbol	Conditions	min	typ	max	Unit
Dimensions	$L \times W \times H$	Typical, see outline drawing	130 x 140 x 48			mm
Clearance distance in air	$d_a$	according to IEC 60664-1 and EN 50124-1	Term. to base:	40		mm
			Term. to term:	26		
Surface creepage distance	$d_s$	according to IEC 60664-1 and EN 50124-1	Term. to base:	64		mm
			Term. to term:	56		
Mass	$m$			1010		g

<sup>7)</sup> Package and mechanical properties according to IEC 60747 – 15

## Electrical configuration




## Outline drawing <sup>2)</sup>




<sup>2)</sup> For detailed mounting instructions refer to ABB Document No. 5SYA2039

**This is an electrostatic sensitive device, please observe the international standard IEC 60747-1, chap. IX.**


**This product has been designed and qualified for Industrial Level.**




**Fig. 1** Typical on-state characteristics, chip level




**Fig. 2** Typical transfer characteristics, chip level




**Fig. 3** Typical output characteristics, chip level




**Fig. 4** Typical output characteristics, chip level




**Fig. 5** Typical switching energies per pulse vs collector current




**Fig. 6** Typical switching energies per pulse vs gate resistor




**Fig. 7** Typical switching times vs collector current




**Fig. 8** Typical switching times vs gate resistor




**Fig. 9** Typical capacitances vs collector-emitter voltage




**Fig. 10** Typical gate charge characteristics




**Fig. 11** Turn-off safe operating area (RBSOA)




**Fig. 12** Typical reverse recovery characteristics vs forward current



**Fig. 13** Typical reverse recovery characteristics vs di/dt




**Fig. 14** Typical diode forward characteristics, chip level



**Fig. 15** Safe operating area diode (SOA)





**Fig. 16** Thermal impedance vs time

**Analytical function for transient thermal impedance:**

$$Z_{th(j-c)}(t) = \sum_{i=1}^n R_i (1 - e^{-t/t_i})$$

	i	1	2	3	4	5
IGBT	R <sub>i</sub> (K/kW)	9.54	3.17	1.56		
	t <sub>i</sub> (ms)	193	21.4	2.78		
DIODE	R <sub>i</sub> (K/kW)	18.7	6.56	3.23		
	t <sub>i</sub> (ms)	192	22.6	3.1		

**Related documents:**

5SYA 2042 Failure rates of HiPak modules due to cosmic rays  
 5SYA 2043 Load - cycle capability of HiPaks  
 5SYA 2045 Thermal runaway during blocking  
 5SYA 2053 Applying IGBT  
 5SYA 2058 Surge currents for IGBT diodes  
 5SYA 2093 Thermal design of IGBT modules  
 5SYA 2098 Paralleling of IGBT modules  
 5SZK 9111 Specification of environmental class for HiPak Storage  
 5SZK 9112 Specification of environmental class for HiPak Transportation  
 5SZK 9113 Specification of environmental class for HiPak Operation (Industry)  
 5SZK 9120 Specification of environmental class for HiPak

We reserve the right to make technical changes or to modify the contents of this document without prior notice.

We reserve all rights in this document and the information contained therein. Any reproduction or utilization of this document or parts thereof for commercial purposes without our prior written consent is forbidden.

Any liability for use of our products contrary to the instructions in this document is excluded.



**ABB Switzerland Ltd**  
**Semiconductors**

Fabrikstrasse 3  
 CH-5600 Lenzburg, Switzerland

Telephone +41 (0)58 586 1419  
 Fax +41 (0)58 586 1306  
 Email [abbsem@ch.abb.com](mailto:abbsem@ch.abb.com)  
 Internet [www.abb.com/semiconductors](http://www.abb.com/semiconductors)