

TECHNICAL DATA SHEET

Chemical resistance guide

This document serves as a guideline only and compatibility should be verified in the application environment to ensure suitability. Many factors can determine the exact suitability; such as temperature, duration of contact, nature of contact such as submersion and concentration of the chemicals involved.

Resistance guide																
Chemicals	Metals							Plastics & Elastomers								
	Aluminum	Carbon Steel	Cast/Ductile Iron	Nickel Plated Brass	303/304 Stainless Steel	1.4301 (V2A)	316 Stainless Steel	1.4401 (V4A)	PA6 PA66 Polyamide	POM Polyacetal	PVC Polyvinylchloride	TPE-U/ TPE-E Polyester	PP Polypropylene	EPR, EPDM	NBR Nitrile	CR Polychloroprene
Acetate Solvents	2	0	0	3	0	3	3	3	0	0	0	2	0	0	0	0
Acetic Acid	2	0	0	3	0	2	0	0	3	0	2	3	1	1	1	1
Acetic Acid — 20%	2	0	0	3	2	3	0	1	3	0	2	3	1	2	-	-
Acetic Acid — 30%	0	-	3	3	3	3	0	2	-	0	2	3	1	2	-	-
Acetic Acid — 50%	0	-	3	3	3	2	0	2	-	1	2	3	0	1	-	-
Acetic Acid — 80%	2	0	0	3	0	2	0	0	-	1	3	3	0	1	-	-
Acetic Acid — Glacial	2	0	0	2	1	3	0	0	3	1	1	2	0	0	-	-
Acetone	2	3	3	3	3	3	2	2	0	1	0	3	0	0	0	0
Acetone Cyanohydrin	2	-	2	3	2	-	-	-	-	-	-	0	-	2	-	-
Acetonitrile (Methyl Cyanide)	3	3	3	3	3	3	3	3	0	-	0	3	0	0	0	2
Acetophenone	2	3	3	3	3	2	3	-	-	-	1	2	0	0	0	-
Acrylonitrile	2	3	3	3	3	3	2	-	3	0	2	0	0	0	0	0
Adipic Acid	2	3	2	3	2	2	3	2	3	0	2	3	3	0	-	-
Alcohol	3	3	3	3	3	3	0	2	3	2	2	2	-	-	-	-
Alcohol: Amyl	2	2	2	3	3	3	3	3	3	3	2	3	2	2	0	0
Alcohol: Benzyl	2	2	2	3	2	2	0	3	3	0	3	1	0	1	1	1
Alcohol: Butyl	2	2	2	3	3	3	0	3	3	0	2	3	3	3	0	0
Alcohol: Diacetone	2	3	2	3	3	3	3	3	2	0	2	2	0	0	0	2
Alcohol: Ethyl	2	2	2	3	3	3	2	3	3	3	3	3	3	3	0	0
Alcohol: Hexyl	3	3	3	3	3	3	3	3	3	0	3	1	3	2	0	0
Alcohol: Isobutyl	2	1	1	3	3	3	2	3	3	2	3	2	1	3	0	0
Alcohol: Isopropyl	2	3	1	3	2	2	0	3	3	3	3	2	1	2	0	0
Alcohol: Methyl	2	3	3	3	3	3	2	3	3	2	3	2	3	3	0	0
Alcohol: Octyl	3	3	3	3	3	3	3	3	3	0	-	3	2	2	0	0
Alcohol: Propyl	3	3	3	3	3	3	2	3	3	0	3	2	3	3	0	0
Aluminum Chloride	0	0	0	0	0	1	0	2	3	1	3	3	3	3	2	2
Ammonia 10%	3	3	3	3	3	3	3	0	3	-	3	3	-	3	-	-
Ammonia Anhydrous	3	3	3	3	3	3	2	0	3	0	3	3	-	2	-	-
Ammonia Liquids	0	-	3	3	3	-	-	0	0	-	3	3	2	3	2	2

Resistance guide																
Chemicals	Metals							Plastics & Elastomers								
	Aluminum	Carbon Steel	Cast/Ductile Iron	Nickel Plated Brass	303/304 Stainless Steel	1.4301 (V2A)	316 Stainless Steel	1.4401 (V4A)	PA6 PA66 Polyamide	POM Polyacetal	PVC Polyvinylchloride	TPE-U/TPE-E Polyester	PP Polypropylene	EPR, EPDM	NBR Nitrile	CR Polychloroprene
Ammonia Liquors	3	-	3	3	3	-	-	-	-	0	-	-	-	-	3	-
Aniline	1	1	1	3	3	2	1	2	2	2	0	1	0	0	0	0
ASTM no.1	3	-	3	3	3	-	-	3	3	3	-	0	3	2	2	
ASTM no.2	3	-	3	3	3	-	-	3	2	3	-	0	3	2	0	
ASTM no.3	3	-	3	3	3	-	-	3	-	3	-	0	3	1	0	
ASTM no.4	3	-	3	3	3	-	-	3	-	0	-	0	2	0	0	
ASTM no.5	3	-	3	3	3	-	-	-	-	3	-	0	3	2	0	
ASTM no.6	3	-	3	3	3	-	-	-	-	3	-	0	0	0	0	
ASTM no.7	3	-	3	3	3	-	-	-	-	3	-	0	2	0	0	
Benzaldehyde	2	3	3	3	2	2	0	3	-	2	0	2	0	0	0	
Benzene	2	3	2	3	2	2	3	3	2	1	0	0	0	0	0	
Blood	-	-	-	3	3	3	-	-	3	-	3	-	-	-	-	
Brake Fluid (Mineral)	3	3	3	3	3	3	2	3	0	0	0	3	1	2	3	
Carbon Tetrachloride	0	0	0	3	2	2	0	2	0	0	0	0	1	0	3	
Caustic	0	-	-	3	3	3	-	-	-	0	-	-	-	-	-	
Chlorinated Water	0	-	-	3	2	2	0	0	0	0	1	0	1	1	0	
Chlorine Water	0	-	-	3	1	1	1	0	0	-	0	1	-	0	-	
Chloroform	0	2	0	3	3	3	0	2	0	0	0	0	0	0	0	
Citric Acid	1	0	0	3	2	3	0	2	3	3	2	3	-	3	-	
Copper Sulfate	-	-	-	3	3	3	1	3	3	2	3	3	-	3	-	
Creosols	2	-	1	3	3	-	-	2	2	-	0	0	0	0	0	
Cresols	2	1	1	3	3	3	0	0	3	0	0	0	-	0	-	
Crude Oil	3	-	2	3	3	3	3	0	-	2	0	0	2	1	0	
Diesel Fuel	3	3	3	3	3	3	3	3	2	2	2	0	-	0	-	
Diethylamine	2	2	0	3	2	2	2	2	-	-	1	2	-	2	-	
Dyes	2	-	2	3	3	3	3	1	-	-	-	-	-	1	-	
Ethane	3	3	3	3	3	3	0	3	-	-	0	0	3	1	2	
Ethanol (Ethyl Alcohol)	2	2	2	3	3	3	1	3	-	3	3	3	3	3	0	
Ethanolamine	2	3	2	3	3	3	3	0	-	-	0	2	2	1	1	
Ether	2	1	1	3	3	3	3	3	-	-	0	1	-	0	-	
Ethyl Ether	1	1	1	2	2	2	2	2	0	-	0	0	0	0	0	
Ethyl Formate	1	-	3	2	2	2	-	3	0	0	-	1	0	2	-	
Ethylene Glycol	2	2	2	3	2	2	2	2	3	1	3	3	3	3	2	
Freon 32	0	3	3	3	3	3	-	3	-	-	-	3	3	3	-	
Gasoline	3	3	3	3	3	3	-	3	2	3	0	0	3	0	1	
Gelatin	2	3	0	3	3	3	2	2	-	2	3	3	3	3	0	
Glycol	2	-	2	2	2	2	1	2	-	-	3	3	-	3	-	
Grapefruit Oil	-	0	0	3	3	3	-	-	3	-	-	-	3	0	-	
Grease	3	3	3	3	3	3	-	0	3	-	-	0	-	0	-	
Heavy Water	3	-	1	2	3	-	-	-	-	2	-	3	3	-	0	
Hexane	3	3	3	3	3	3	2	1	2	3	1	0	3	0	2	
Hexanol	3	-	3	3	3	-	-	3	-	0	3	3	3	2	0	
Hexanol Tertiary	3	3	3	3	3	3	3	3	-	-	2	-	-	-	-	
Hexyl Alcohol	3	-	-	2	3	-	-	-	-	-	3	-	-	2	-	
Hexyl Alcohol	3	-	3	2	3	-	-	-	-	0	-	1	2	2	0	
Hexylene Glycol (Brake Fluid)	3	-	3	2	3	-	-	-	-	0	-	1	3	3	-	
Hydraulic Oil (Petro)	3	3	3	3	3	3	3	2	-	-	0	0	-	3	-	
Hydraulic Oil (Petroleum Base)	3	3	3	3	3	3	3	1	-	3	0	0	-	2	-	
Hydraulic Oil (Petroleum)	3	-	3	3	3	3	3	2	-	3	0	0	3	2	-	
Hydraulic Oil (Synthetic)	3	3	3	3	3	3	3	2	-	3	0	0	0	0	2	

Resistance guide																
Chemicals	Metals						Plastics & Elastomers									
	Aluminum	Carbon Steel	Cast/Ductile Iron	Nickel Plated Brass	303/304 Stainless Steel	1.4301 (V2A)	316 Stainless Steel	1.4401 (V4A)	PA6 PA66 Polyamide	POM Polyacetal	PVC Polyvinylchloride	TPE-U/TPE-E Polyester	PP Polypropylene	EPR, EPDM	NBR Nitrile	CR Polychloroprene
Hydrazine	2	0	0	3	3	3	-	2	-	0	0	3	2	1	0	
Hydrochloric Acid - 10%	0	0	0	3	0	0	0	0	3	0	3	3	-	0	-	
Hydrochloric Acid - 37%	0	0	0	3	0	0	0	0	3	0	1	1	2	0	0	
Hydrogen Peroxide - 30%	3	2	0	3	2	2	0	0	3	0	2	2	-	0	-	
Hydrogen Peroxide - 90%	3	-	0	2	3	-	0	0	3	0	3	1	-	0	-	
Isopropyl Alcohol	3	3	3	3	3	3	0	3	-	3	3	2	3	2	0	
Isopropyl Amine	-	-	3	3	3	-	-	-	-	-	-	-	0	-	-	
Isopropyl Chloride	0	-	3	3	3	3	-	3	-	-	0	0	0	0	0	
Isopropyl Ether	2	3	3	3	3	3	3	0	-	-	0	0	2	0	2	
Jet Fuel (JP1 to JP6)	3	3	3	3	3	3	1	3	-	-	0	0	-	0	-	
Kerosene	3	3	3	3	3	3	3	3	3	1	0	0	3	0	2	
Ketchup	-	-	-	3	3	3	3	3	3	-	-	3	-	3	-	
Ketones	2	3	3	3	3	3	3	0	0	0	0	3	0	0	0	
Lacquers	3	1	1	2	3	3	3	0	0	0	0	0	0	0	0	
Lactic Acid	0	0	0	3	2	2	0	1	-	0	2	3	-	1	-	
Lactic Acid - 5% Solution	1	-	0	3	3	-	-	3	-	0	3	3	3	3	2	
Lard	3	3	3	3	2	3	3	2	-	2	2	0	-	0	-	
Lard Oil (Cold)	3	3	3	3	3	3	-	3	-	-	-	0	-	2	-	
Lard Oil (Hot)	3	3	3	3	3	3	-	3	-	2	2	0	3	2	1	
Latex	3	-	-	3	3	3	3	1	-	-	3	3	3	2	0	
Lubricants	3	3	3	3	3	3	3	3	3	3	2	0	-	0	-	
Lubricants (Petroleum)	1	-	3	3	3	3	3	3	3	3	0	0	3	2	2	
Lubricating Oil	3	3	3	3	3	3	3	3	3	3	3	0	-	2	-	
Methanol	2	3	3	3	3	3	2	3		2	3	3	3	3	0	
Methyl Acetate	2	2	2	2	3	2	3	2	0	1	0	1	0	0	0	
Methyl Acetone	3	3	3	2	3	3	3	0		-	0	3	1	0	-	
Methyl Bromide	0	3	3	3	3	3	0	0	0	0	0	0	2	0	0	
Methyl Ethyl Ketone (MEK)	2	3	3	3	3	3	1	1	0	2	0	3	0	0	0	
Methyl Formate	3	-	2	2	2	2	-	3	-	-	-	1	0	2	0	
Nitric Acid - 10%	0	0	0	1	3	3	0	0	3	0	0	2	-	2	-	
Nitric Acid - 70%	3	-	0	1	3	3	0	0	0	0	0	0	-	0	-	
Olive Oil	3	3	3	3	2	3	3	3		-	3	0	3	0	3	
Ozone	2	0	1	3	2	2	0	0		1	0	3	0	1	3	
Paint Thinner, Duco	0	2	2	3	2	3	3	3	0	-	0	0	0	0	0	
Paraffin	3	3	3	3	3	3	3	3	3	-	3	0	3	2	3	
Petroleum	0	-	1	3	3	3	3	2	2	2	2	0	-	2	-	
Petroleum Ether	2	-	2	3	3	3	3	3	2	-	3	0	3	0	2	
Phenol	2	-	0	3	3	-	-	3	2	0	1	-	0	0	0	
Phenol (10%)	3	0	0	3	2	2	0	2	2	-	2	2	-	0	-	
Phosphoric Acid - 10%	0	-	0	3	3	-	0	-	3	-	3	3	-	2	-	
Phosphoric Acid - 20%	0	-	0	3	3	2	0	0	3	-	3	3	2	2	1	
Salt Brine	1	0	0	1	2	0	3	2	2	3	3	3	-	3	-	
Salt Water	0	0	0	1	1	2	3	3	2	3	3	3	3	2	0	
Sea Water	0	0	0	1	1	1	3	3	3	3	3	3	3	2	3	
Sea Water (Brine)	3	-	1	1	3	-	3	3	3	-	3	3	-	2	-	
Sewage	0	0	0	2	3	3	-	3		2	3	1	3	2	0	
Silicone	2	3	3	3	3	3	3	3		3	3	3	-	3	-	
Silicone Grease	-	-	-	3	-	-	-	3		3	-	3	3	3	3	
Silicone Oil	2	3	2	3	3	3	3	3		2	3	3	3	0	3	
Silver Nitrate	0	1	0	3	2	2	3	3		0	2	3	2	3	3	

Resistance guide																
Chemicals	Metals							Plastics & Elastomers								
	Aluminum	Carbon Steel	Cast/Ductile Iron	Nickel Plated Brass	303/304 Stainless Steel	1.4301 (V2A)	316 Stainless Steel	1.4401 (V4A)	PA6 PA66 Polyamide	POM Polyacetal	PVC Polyvinylchloride	TPE-U/ TPE-E Polyester	PP Polypropylene	EPR, EPDM	NBR Nitrile	CR Polychloroprene
Skydol 7000	-	-	-	3	3	-	-	3		0	-	3	0	0	0	0
Skydrol	-	-	-	3	-	-	1	-		2	-	3	-	0	-	-
Skydrol 500	-	-	-	3	3	-	1	3		1	-	3	0	0	0	0
Skydrol Hydraulic Fluid	-	-	-	3	3	-	1	-		-	-	3	-	0	-	-
Sodium Chloride	1	0	0	1	1	1	3	2		3	3	3	3	3	3	3
Sodium Hydroxide	0	-	2	3	3	-	1	0	2	-	3	3	-	2	-	-
Sodium Hydroxide (< 10%) (Caustic Soda)	-	-	-	3	-	-	-	-	3	-	-	-	-	-	-	-
Sodium Hydroxide (< 50%) (Caustic Soda)	-	-	-	3	-	-	-	-	3	-	-	-	-	-	-	-
Sodium Hydroxide (20%)	0	3	2	3	2	2	3	3	3	2	3	2	3	2	2	2
Sodium Hydroxide (50%)	0	0	0	3	2	2	3	3	3	1	3	2	0	1	2	2
Sulfur Dioxide	0	-	0	0	0	3	1	0	0	0	3	2	0	2	1	1
Sulfur Dioxide (dry)	2	3	3	0	0	3	2	2	3	1	3	3	-	0	-	-
Sulfur Dioxide Gas Dry	0	-	2	0	3	3	2	2	3	0	1	3	-	0	-	-
Sulfuric Acid - Concentrated	-	-	-	0	-	-	0	0	0	0	2	0	-	0	-	-
Sulfuric Acid (<10%)	0	1	0	0	0	1	1	0	2	3	3	3	0	0	0	0
Sulfuric Acid (10-75%)	0	0	0	0	0	0	0	0	1	-	3	2	-	0	-	-
Sulfuric Acid (75-100%)	0	0	0	0	1	0	0	-	0	1	1	2	-	0	-	-
Sulfuric Acid (hot concentrated)	0	0	0	0	0	1	0	-	0	-	0	0	-	0	-	-
Syrup	3	-	-	3	3	3	-	3	3	-	3	3	3	2	-	-
Toluene	3	-	3	3	-	3	3	-	0	-	0	-	-	0	-	-
Transformer Oil	3	-	2	3	3	3	3	1	-	-	0	0	3	1	3	3
Trichlorethylene	0	-	1	3	-	3	3	-	0	-	2	-	-	0	-	-
Turbine Oil	3	3	3	3	3	3	3	3	-	-	2	0	2	0	3	3
Turpentine	3	-	2	3	3	3	2	3	2	2	0	0	3	0	0	0
Unleaded Gasoline	3	-	3	3	-	3	3	-	-	-	0	-	-	0	-	-
Urea	2	-	2	2	2	2	1	3	3	2	3	3	2	2	2	2
Urine	2	3	2	3	3	3	2	1	-	-	3	3	3	0	-	-
Vegetable Oil	2	2	2	3	3	3	3	3	-	-	0	0	3	0	3	3
Vinyl Acetate	2	2	1	3	2	2	-	-	0	-	0	2	0	0	0	0
Water	3	0	0	3	3	3	-	3	3	3	2	3	-	3	-	-
White Spirit	-	-	-	3	-	3	3	3		3	3	-	-	-	-	-
Zinc Chloride	0	0	0	3	0	0	1	0	3	2	3	3	3	2	3	3

ABB Inc.
Electrification products
Memphis, Tennessee
USA

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB Inc. does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB Inc. Copyright© 2017 ABB Inc. All rights reserved.

