



# FurseWELD

## Cable to steel surface & pipe CS8 & CS9

### Cable to steel surface & pipe CS8 - FurseWELD



	Stranded/solid circular conductor size A (mm <sup>2</sup> )	Mould part no.	Order code	Powder cartridge part no.	Handle clamp part no.
	16 *	CS8-2-16	7TCA083910R2123	45P10	HCPK2
	25	CS8-2-25	7TCA083910R2124	45P10	HCPK2
	35	CS8-2-35	7TCA083910R2125	45P10	HCPK2
	50	CS8-2-50	7TCA083910R2127	45P10	HCPK2
	70	CS8-2-70	7TCA083910R2128	65P10	HCPK2
	95	CS8-2-95	7TCA083910R2129	90P10	HCPK2
	120	CS8-4-120	7TCA083910R2130	115P10	HCPK4
	150	CS8-4-150	7TCA083910R2131	150P10	HCPK4
	185	CS8-4-185	7TCA083910R2132	200P10	HCPK4
	240	CS8-4-240	7TCA083910R2133	200P10	HCPK4
	300	CS8-4-300	7TCA083910R2134	250P10	HCPK4



Special moulds for all FurseWELD products can be manufactured to meet specific customer applications on request

\*1 x S103 Sleeve required when joining conductors 16 mm<sup>2</sup> or smaller


For order codes of powder cartridges and handle clamps, see pages 49-50

FurseWELD moulds should only be used with FurseWELD powders, handle clamps and accessories. If moulds, powders, handle clamps and accessories from other manufacturers are utilized, we cannot guarantee the safe use or the integrity of the completed joint


FurseWELD moulds for use with stranded conductor are designed for use with non-compacted conductor to BS EN 60228. If a mould for compacted conductor is required, please contact your local representative

Conductors must be installed in the orientation shown to achieve the correct connection

### Cable to steel surface & pipe CS9 - FurseWELD



	Stranded/solid circular conductor size A (mm <sup>2</sup> )	Mould part no.	Order code	Powder cartridge part no.	Handle clamp part no.
	16 *	CS9-2-16	7TCA083910R2498	45P10	HCPK2
	25	CS9-2-25	7TCA083910R3011	45P10	HCPK2
	35	CS9-2-35	7TCA083910R2137	45P10	HCPK2
	50	CS9-4-50	7TCA083910R2140	90P10	HCPK4
	70	CS9-4-70	7TCA083910R2141	115P10	HCPK4
	95	CS9-4-95	7TCA083910R2142	115P10	HCPK4
	120	CS9-4-120	7TCA083910R2138	150P10	HCPK4
	150	CS9-4-150	7TCA083910R3050	200P10	HCPK4
	185	CS9-4-185	7TCA083910R2139	250P10	HCPK4
	240	CS9-5-240	7TCA083910R2281	2 x 150P10	HCPK5



Special moulds for all FurseWELD products can be manufactured to meet specific customer applications on request

\*2 x S103 Sleeve required when joining conductors 16 mm<sup>2</sup> or smaller

For order codes of powder cartridges and handle clamps, see pages 49-50

FurseWELD moulds should only be used with FurseWELD powders, handle clamps and accessories. If moulds, powders, handle clamps and accessories from other manufacturers are utilized, we cannot guarantee the safe use or the integrity of the completed joint

FurseWELD moulds for use with stranded conductor are designed for use with non-compacted conductor to BS EN 60228. If a mould for compacted conductor is required, please contact your local representative

Conductors must be installed in the orientation shown to achieve the correct connection