


Substation

Our extensive substation solutions — encompassing weldment and bolted connections up to 500kV, current-limiting fuses, capacitor and reactor switches and more — help you improve reliability and increase efficiency.



- 1** Blackburn® flexible braid
- 2** Homac® bolted elbow, pipe to pipe
- 3** Homac corona bell, drive fit
- 4** Homac bolted expansion bus support, pipe to insulator
- 5** Homac bolted ground connector, two or three cables, parallel to pipe or rod
- 6** Homac welded cable jumper, flat to flat
- 7** Homac bolted tee, cable to cable
- 8** Homac terminal, two cables to flat
- 9** Homac bolted terminal, two cables to flat
- 10** Homac bolted terminal, pipe to flat
- 11** Homac U-bolt parallel clamp, cable to cable
- 12** Homac bolted stud connector
- 13** Homac bolted bus support, cable to insulator
- 14** Homac bolted cable spacer, two cables
- 15** Homac EHV bolted bus support, two cables to insulator
- 16** Homac hook-on bus support, weld or slide, pipe to insulator
- 17** Homac bolted terminal, pipe to center-formed flat
- 18** Homac aluminum compression terminal
- 19** Elastimold® TCJ cable joint
- 20** Elastimold vacuum recloser
- 21** Elastimold Ranger2 cold-shrink termination
- 22** Elastimold 69 kV transmission cable termination
- 23** Joslyn Hi-Voltage™ VBM capacitor switches
- 24** Hi-Tech® current-limiting substation fuse