



Test Report				Date of issue: 28.8.2013					
				Serial No.: 3GF11094416					
				Type: M3GP 160MLC 6 IMB3/IM1001					
				Product Code: 3GGP163430-ADD					
				Protection type: Ex nA II C T3 Gc					
				Cert. No.: LCIE 13 ATEX 1034 X					
				IECEX LCIE 13.0047X					
Rating:									
	V	Hz	kW	r/min	A	cos φ	Duty		
3-Motor	690	Y 50	14	969	17,5	0,75	S1		
Insul.cl.F	400	D 50	14	969	30,2	0,75	S1		
IP55	415	D 50	14	971	29,9	0,73	S1		
Eff class IE1						400V 50Hz: IE1 - 89.2(100%) - 89.4(75%) - 88.0(50%)			
Resistance			Insulation resistance at 47,5 °C						
Line			3000 MΩ			1000 V			
Ambient: 21,0 °C									
U ₁ - V ₁			0,40000 Ω						
U ₁ - W ₁			0,40020 Ω						
V ₁ - W ₁			0,40020 Ω						
				High-voltage test winding		2900 V 1 s			
Test	Torque [Nm]	Line U[V]	f[Hz]	Input I[A]	P1 [kW]	Output P2 [kW]	n[r/min]	cos φ	η [%]
No load test		400,0 D	50	17,3	0,65		998	0,05	
Locked rotor test		84,5 D	50	30,2	1,65		0	0,37	
Thermal test (100% load)	138,0	400,0 D	50	30,1	15,7	14,0	973	0,75	89,1
Partial load points:									
~75% load	103,3	400,0 D	50	25,2	11,7	10,5	981	0,67	89,4
~50% load	68,5	400,0 D	50	20,9	7,92	7,00	987	0,55	88,4
~25% load	34,4	400,0 D	50	17,9	4,23	3,50	993	0,34	82,8
Temperature rise at rated load.			[°C]	[K]	Method		Measurement method		
Stator winding :				73,6	1		1 Resistance		
Frame :				35,8	2		2 Thermometer		
Bearing D-end :				39,7	2		3 Thermocouples		
Rotor :				92,0	3				
Ambient Temperature :			25,0		2				
Manufactured and tested in accordance with rules of IEC 60034-1 and IEC 60034-2-1. PLL determined from residual loss.									
On behalf of customer									
On behalf of manufacturer		Date of test		14.2.2012					
Tested by ABB Oy, Motors and Generators, Vaasa, Finland						Telephone +358 10 2211			
						Telefax +358 10 22 47372			

Computer print-out valid without signature.