

BALDOR® • RELIANCE

Product Information Packet

ECP83582T-4

1HP,1160RPM,3PH,60HZ,145T,0526M,TEFC,F1

Part Detail									
Revision:	-	Status:	PRD/A	Change #:		Proprietary:	No		
Type:	AC	Prod. Type:	0526M	Elec. Spec:	05WGX259	CD Diagram:			
Enclosure:	TEFC	Mfg Plant:		Mech. Spec:	05E811	Layout:			
Frame:	145T	Mounting:	F1	Poles:	06	Created Date:	08-05-2012		
Base:	RG	Rotation:	R	Insulation:	F	Eff. Date:	08-10-2012		
Leads:	3#18	Literature:		Elec. Diagram:		Replaced By:			
Nameplate NP2162E									
CAT.NO.	ECP83582T-4								
SPEC.	05E811X259G1								
HP	1	T. CODE				T3			
VOLTS	460								
AMP	1.7								
RPM	1160								
FRAME	145T	HZ			60	PH		3	
SER.F.	1.15	CODE			K	DES		B	CL F
NEMA-NOM-EFF	82.5	PF			66				
G.MIN.EFF	80.0	CC			010A				
RATING	40C AMB-CONT								
DE	6205	ODE			6205				
ENCL	TEFC	SN							

Nameplate NP2113E			
SPEC.	05E811X259G1		
MOTOR WEIGHT	61 LBS		
GREASE	POLYREX EM		
MAX. KVAR	.59		
# OF ROTOR BARS	27	# OF STATOR SLOTS	36
BLANK			
HTR-VOLTS	N/A	HTR-AMPS	N/A
MAX. SPACE HEATER TEMP.	N/A		

Parts List		
Part Number	Description	Quantity
SA249005	SA 05E811X259G1	1.000 EA
RA235871	RA 05E811X259G1	1.000 EA
35FN3002A05SP	EXFN, PLASTIC, 6.376 OD, .638 ID	1.000 EA
HW3201A05	3/8-16 EYEBOLT	1.000 EA
06CB1001A01G	CONDUIT BOX, MACH GRAY	1.000 EA
RM1016	LEAD SEPARATOR GASKET - 305/306 C.P.MOTO	1.000 EA
51XW2520A12	.25-20 X .75, TAPTITE II, HEX WSHR SLTD	2.000 EA
11XW1032G06	10-32 X .38, TAPTITE II, HEX WSHR SLTD U	1.000 EA
HW3001B01	003SS CUP WASHER, FOR #8 SCREW	1.000 EA
10XN2520S06	1/4 20X3/8 HX HD CAP S.S.	2.000 EA
WD1000B16	KPA-4C BURNDY TERMINAL	2.000 EA
51XN1032A20	10-32 X 1 1/4 HX WS SL SR	2.000 EA
05EP1100A02G	FREP TEFC 203,GRSR,RLF,DRAIN FITTING,INP	1.000 EA
HW4601A22	INPRO SEAL, 205 BRG, VBX	1.000 EA
HW4600B36SP	V-RING SLINGER 1.188 X 1.690 X 0.240	1.000 EA
HW4500A01	1641B(ALEMITE)400 UNIV, GREASE FITT	1.000 EA
HA4051A00	PLASTIC CAP FOR GREASE FITTING	1.000 EA
HW4500A17	317400 ALEMITE GREASE RELIEF	1.000 EA
HA4010A01	DRAIN PLUG,416 S.S.,W/ 1/4-28 THD & .076	1.000 EA
HW5100A05	WVY WSHR F/205 & 304 BRGS	1.000 EA
05EP1100A01G	PUEP ENCL 205,BRG RET,GRSR,RLF,DRAIN FIT	1.000 EA
HW4601A22	INPRO SEAL, 205 BRG, VBX	1.000 EA
HW4600B36SP	V-RING SLINGER 1.188 X 1.690 X 0.240	1.000 EA
HW4500A01	1641B(ALEMITE)400 UNIV, GREASE FITT	1.000 EA


Parts List (continued)		
Part Number	Description	Quantity
HA4051A00	PLASTIC CAP FOR GREASE FITTING	1.000 EA
HW4500A17	317400 ALEMITE GREASE RELIEF	1.000 EA
HA4010A01	DRAIN PLUG,416 S.S.,W/ 1/4-28 THD & .076	1.000 EA
51XN1032A20	10-32 X 1 1/4 HX WS SL SR	2.000 EA
HA3100A37	THRUBOLT 10-32 X 8.500	4.000 EA
XY1032A02	10-32 HEX NUT DIRECTIONAL SERRATION	4.000 EA
35FH1000A19G	35FH1000A19 W/GRAY FLUIDIZ	1.000 EA
10XN2520A16	1/4-20 X 1 HEX HEAD CAP SCR, ZINC PLATED	3.000 EA
HW1001A25	LOCKWASHER 1/4, ZINC PLT .493 OD, .255 I	3.000 EA
WD4100A03	DE-750 HEYCO PLUG 62MP0750 MICRO PLASTIC	1.000 EA
06CB1503A01G	LIPPED CONDUIT BOX LID, MACH GRAY EPOXY	1.000 EA
06GS1009	GASKET, KOBX LID, 1/8" THICK BLACK NEOPR	1.000 EA
10XN2520A12	O1/4-20X 3/4 HEX HEAD CAP	2.000 EA
HW1001A25	LOCKWASHER 1/4, ZINC PLT .493 OD, .255 I	2.000 EA
MJ5004A59	ADHESIVE LOCTITE #401 SURFACE INSENSITIV	0.010 EA
HW2501D13SP	KEY, 3/16 SQ X 1.375	1.000 EA
HA7000A01	KEY RETAINER 7/8" DIA SHAFT	1.000 EA
MJ5001A01	46-665 RED SEALER	0.001 QT
MJ1000A73	INPRO P-80 ASSEMBLY LUB./ 1 QT. CONTAIN	0.001 QT
85XU0407S04	4X1/4 U DRIVE PIN STAINLESS	4.000 EA
LB1002	LABEL,MARINE DUTY (ON ROLLS)	1.000 EA
LB1115	LABEL,LIFTING DEVICE	1.000 EA
LT0019A00	MOTOR NO-LOAD PERFORMANCE DATA SHEET	1.000 EA
WD1000D21	TRM,T&B #B71M,RING,18-14,.25,NON-INSL	3.000 EA


Parts List (continued)		
Part Number	Description	Quantity
MJ1000A75	GREASE, POLYREX EM EXXON	0.050 LB
51XB1214A16	12-14X1.00 HXWSSLD SERTYB	1.000 EA
MG1025N19	PAINT, 778.50 WILKO, RELIANCE ELEC GREEN	0.022 GA
LB1119	WARNING LABEL	1.000 EA
LC0006	CONNECTION LABEL	1.000 EA
LB1449	DIV-2/NEC WARNING LABEL	1.000 EA
LB1357	ENERGY GUIDE LABEL (BOX LABEL)	1.000 SH
LB1125C02	SUPER-E (STOCK CTN LABEL SUPER-E WITH FL	1.000 EA
NP2162E	SS IEEE841 DIV-2 UL CSA-C US EEV PREM	1.000 EA
NP2113E	SS IEEE841 AUX DATA INFORMATION SURFACE	1.000 EA
36PA1000	PACK GROUP W/LB5001	1.000 EA

Performance Data at 460V, 60Hz, 1.0HP (Typical performance - Not guaranteed values)


General Characteristics							
Full Load Torque:		4.53 LB-FT		Start Configuration:		DOL	
No-Load Current:		1.16 Amps		Break-Down Torque:		14.6 LB-FT	
Line-line Res. @ 25°C.:		17.6 Ohms A Ph / 0.0 Ohms B Ph		Pull-Up Torque:		11.1 LB-FT	
Temp. Rise @ Rated Load:		35 C		Locked-Rotor Torque:		12.0 LB-FT	
Temp. Rise @ S.F. Load:		41 C		Starting Current:		10.4 Amps	
Load Characteristics							
% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor:	27.0	45.0	57.0	66.0	72.0	75.0	70.0
Efficiency:	70.2	80.0	82.7	83.1	81.8	80.0	82.3
Speed:	1192.0	1182.0	1171.0	1160.0	1146.0	1131.0	1152.0
Line Amperes:	1.19	1.31	1.49	1.72	2.0	2.34	1.89

Performance Graph at 460V, 60Hz, 1.0HP Typical performance - Not guaranteed values





CD0006



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS

REV. LTR: D BY: JLP REVISED: 01/21/99 4:02 TDR: 0171435

9000D

FILE: AAA00005141

MDL: -

MTL: -

BALDOR ELECTRIC Co.

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

CD0006

LT0019A00																	
NOTE: 1) BALDOR LOGO, "NO LOAD", AND "VIBRATION (IN/SEC.)" TO BE CENTERED ON PAGE. 2) "IEEE", "SPECIAL TEST", AND "OTHER" TO BE $\frac{3}{16}$" HIGH. 3) "HEATER RESISTANCE (WHEN REQ'D)" AND "LT0019A00" TO BE $\frac{3}{32}$" HIGH. 4) ALL OTHER LETTERING TO BE $\frac{1}{8}$" HIGH.																	
MTL: 5.5" X 7" 2 PART CARBONLESS WHITE/MANILA																	
<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td colspan="2" style="padding: 2px;">REV. DESC: ADD DIMENSIONS AND MATERIAL INFO</td> <td rowspan="4" style="text-align: center; vertical-align: middle; padding: 10px;"> BALDOR MOTOR NO LOAD PERFORMANCE DATA SHEET SH 1 of 1 </td> </tr> <tr> <td style="padding: 2px;">REV. LTR: D</td> <td style="padding: 2px;">VERSION: 01</td> </tr> <tr> <td colspan="2" style="padding: 2px;">TDR: 000000724943</td> </tr> <tr> <td colspan="2" style="padding: 2px;">FILE: \AAA\00070\447</td> </tr> <tr> <td colspan="2" style="padding: 2px;">REVISED: 04:02:06 08/22/2012</td> <td></td> </tr> <tr> <td colspan="2" style="padding: 2px;">MTL: 5.5 X 7 2 PART CARBONLESS WHITE/MANILA</td> <td style="padding: 2px;">BY: ENJERWO</td> </tr> </table>			REV. DESC: ADD DIMENSIONS AND MATERIAL INFO		BALDOR MOTOR NO LOAD PERFORMANCE DATA SHEET SH 1 of 1	REV. LTR: D	VERSION: 01	TDR: 000000724943		FILE: \AAA\00070\447		REVISED: 04:02:06 08/22/2012			MTL: 5.5 X 7 2 PART CARBONLESS WHITE/MANILA		BY: ENJERWO
REV. DESC: ADD DIMENSIONS AND MATERIAL INFO		BALDOR MOTOR NO LOAD PERFORMANCE DATA SHEET SH 1 of 1															
REV. LTR: D	VERSION: 01																
TDR: 000000724943																	
FILE: \AAA\00070\447																	
REVISED: 04:02:06 08/22/2012																	
MTL: 5.5 X 7 2 PART CARBONLESS WHITE/MANILA		BY: ENJERWO															