


We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden.
© ABB '19

On-load tap-changer type (V)UCGL./F, (V)UCLL./F, UCCL./F,
11 positions, linear switching.
Max. effective No. of turns in pos. 1.
The tap-changer is delivered set in pos. 6,
the preceding pos. was 5.

Lindningskopplare typ (V)UCGL./F, (V)UCLL./F, UCCL./F,
11 lägen, linjär koppling.
Max antal effektiva varv i läge 1.
Lindningskopplaren levereras inställd i läge 6,
föregående läge var 5.



Pos. Läge	Tap selector and diverter switch connect	
1	1-V-x	30
2	2-H-v	
3	3-V-x	
4	4-H-v	
5	5-V-x	
6	6-H-v	
7	7-V-x	
8	8-H-v	
9	9-V-x	
10	10-H-v	
11	11-V-x	

The tap-changer is shown in pos. 6,
the preceding pos. was 5.
The tap selector is seen from above.
Contact arm V is located above contact arm H.

Lindningskopplaren visad i läge 6,
föregående läge var 5.
Väljaren sedd uppifrån.
Kontaktarm V ligger över kontaktarm H.

Continuous lines show leads included in the
tap-changer. Dashed lines show leads belonging
to the cleats and leads.

Heldragna linjer visar ledare som ingår i
lindningskopplaren. Streckade linjer visar
ledare som tillhör anslutningsdonet.

Sheet	Cont						
	Year	Week					
Form No.	Dept						
	Rev Ind	Revision	Appd	Year	Week		
Design checked by	Accepted by qual control	Accepted for prod by		Description (English)		DATAORIGINAL	
	L.Oberg	M.Haggmar		CONNECTION DIAGRAM			
	Design checked by	Drawn by	Description (own language)		File name		
Drawn by	H.Sundberg	A.Wang	KOPPLINGSSHEMA				
	Drawing checked by	Issued by Dept	Year	Week			
ABB	N.Gustavsson	CO/TK	14	02	1ZSC004307-AAG		
	Lang	Sheet					
Rev Ind	Cont						