Ref. Certif. No.

IT-IMQ-25263

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Residual current operated circuit-breakers without integral overcurrent protection for household and similar uses (RCCBs)
Name and address of the applicant	ABB S.p.A. Via Vittor Pisani 16, 20124 Milano (MI) Italy
Name and address of the manufacturer	ABB S.p.A. Viale dell'Industria, 18, 20009 Vittuone (MI) Italy
Name and address of the factory *Note: When more than one factory, please report on page 2*	ABB S.p.A. Via Ardeatina 2491, 00134 Santa Palomba (RM) Italy ☐ Additional information on page 2
Ratings and principal characteristics	2P (Un = 230 V) or 3P+N (Un = 400 V); type A, AC, AS or ACS; In = 16, 25, 32, 40 or 63 A; IΔn = 10, 30, 100, 300, 500 or 1000 mA Im = 1000 A; IΔm = 1000 A; Inc = 10000 A; IΔc = 10000 A (see also pages 4 and 10 of Test Report PB24-0110140-01)
Trademark / Brand (if any)	ABB
Customer's Testing Facility (CTF) Stage used	CTF Stage 2
Model / Type Ref.	F200 series (see also Additional Sheet)
Additional information (if necessary may also be reported on page 2)	- ☐ Additional information on page 2
A sample of the product was tested and found to be in conformity with	IEC 61008-1:2010, IEC 61008-1:2010/AMD1:2012, IEC 61008-1:2010/AMD2:2013, IEC 61008-2-1:1990 National differences: EU Group Differences, AU, BE, CN, NZ
As shown in the Test Report Ref. No. which forms part of this Certificate	PB21-0069432-02-00, from PB21-0069432-02-01 to PB21-0069432-02-30 and PB24-0110140-01

This CB Test Certificate is issued by the National Certification Body

IMQ S.p.A.
Via Quintiliano 43
Milano, 20138
Italy

Date: 2024-12-20

Signature: Fabio Taormina

Description of the code of RCCBs F200 series

F20 [ ] [ ] - [ ] / [ ] [ ]

Other characteristics:
- G = type G (1)
- AP-R = type AP-R (2)
- T = type T (3)
- TG = type T and type G

Rated residual current:
- 0,01 = 10 mA
- 0,03 = 30 mA
- 0,1 = 100 mA
- 0,3 = 300 mA
- 0,5 = 500 mA
- 1 = 1000 mA

Rated current:
- 16 = 16 A
- 25 = 25 A
- 32 = 32 A
- 40 = 40 A
- 63 = 63 A

Operating characteristic:
- A = type A
- AC = type AC
- AS = type AS
- ACS = type ACS

Number of poles:
- 2 = 2 poles
- 4 = 3 poles + neutral

Basic reference of the series
- F20

(1) – Type G RCCBs are RCCBs complying with Austrian standard ÖVE/ÖNORM E8601:2018

(2) – Type AP-R RCCBs are RCCBs with intentional short time delay (not type S for selectivity)

(3) – Type T RCCBs are RCCBs with rated current 25 A or 40 A constructively identical to the RCCB with rated current 40 A and 63 A respectively and with the same other characteristics (e.g. RCCB F204-AC 25A / 0,03A T is identical to RCCB F204-AC 40A / 0,03A)