



Test Report				Date of issue: 4.6.2014					
				Serial No.: 3GF11094437					
				Type: M3JP 160MLA 8 IMB3/IM1001					
				Product Code: 3GJP164410-ADH					
				Protection type: Ex d IIB T4 Gb					
				Cert. No.: LCIE 11 ATEX 3087X / IECEx LCI 09.0008X					
Rating:									
	V	Hz	kW	r/min	A	cos φ	Duty		
3~Motor	400	D	50	4	722	9,3	0,71 S1		
Insul.cl.F	415	D	50	4	724	9,1	0,70 S1		
IP55	690	Y	50	4	722	5,4	0,71 S1		
400 V 50Hz : 86.7(100%) - 87.4(75%) - 86.6(50%)									
Resistance		Ambient: 22,0 °C		Insulation resistance at 31,5 °C		Overload			
Line				46000 MΩ		1000 V			
U <sub>1</sub> - V <sub>1</sub>		1,94900 Ω				Torque 160 % 15s			
U <sub>1</sub> - W <sub>1</sub>		1,94900 Ω							
V <sub>1</sub> - W <sub>1</sub>		1,94800 Ω							
				High-voltage test winding		2900 V 1 s			
Test	Torque [Nm]	Line U[V]	f[Hz]	Input I[A]	P1 [kW]	Output P2 [kW]	η[r/min]	cos φ	η [%]
No load test		400,1 D	50	5,60	0,28		748	0,07	
Locked rotor test		127,9 D	50	9,29	0,80		0	0,39	
Thermal test (100% load)	52,9	400,0 D	50	10,3	4,91	4,00	705	0,69	81,4
Partial load points:									
~75% load	39,6	400,0 D	50	8,43	3,62	3,00	719	0,62	82,9
~50% load	26,3	400,0 D	50	6,96	2,43	2,00	731	0,50	82,3
~25% load	13,1	400,0 D	50	5,93	1,32	1,00	741	0,32	75,7
Temperature rise at rated load.		[°C]		[K]	Method		Measurement method		
Stator winding :				44,5	1		1 Resistance		
Frame :				27,7	2		2 Thermometer		
Bearing D-end :				26,5	2		3 Thermocouples		
Rotor :				49,2	3				
Ambient Temperature :		25,0			2				
Manufactured and tested in accordance with rules of IEC 60034-1 and IEC 60034-2-1. PLL determined from residual loss.									
On behalf of customer									
On behalf of manufacturer		Date of test		30.3.2012					
Tested by ABB Oy, Motors and Generators, Vaasa, Finland						Telephone +358 10 2211 Telefax +358 10 22 47372			

Computer print-out valid without signature.