

COMPACT CONVERTER

## BORDLINE® CC1500 DC\_3kV

For Intercity regional trains with 3 kVdc line voltage



BORDLINE® CC1500 DC converts the power from the 3 kVdc overhead catenary supply into propulsion power required for driving the the traction motors and generates auxiliary power for onboard consumers (AC, integrated battery charger optional).

—  
BORDLINE® CC1500 DC for double-deck electric multiple unit

### Characteristics

- Well proven three-level converter topology
- Highly energy-efficient
- Motor and line friendly performance

### System overview

BORDLINE® CC1500 DC Compact Converter is connected to the 3 kVdc catenary via an external line inductor and the main circuit breaker.

BORDLINE® CC1500 DC consists of:

- 1 propulsion converter
- 1 braking chopper
- Integrated auxiliary power converter (fixed and variable frequency)
- Integrated battery charger optional
- AC 800PEC control module

### Propulsion converter

BORDLINE® CC1500 DC Compact Converter is a rugged unit based on modern 3.3 kV IGBTs. It can control either one or two motors in parallel. This Compact Converter makes use of ABB's well-proven three-level topology, which has several advantages over conventional two-level solutions: It is better for the motor, better for the grid, and it saves energy!

### Braking chopper

In case the DC catenary is not receptive for recuperative energy, a braking chopper with corresponding resistors is installed. The braking chopper is able to consume the total braking energy in order to ensure safe operation in all cases.

### Auxiliary converter

The auxiliary converter generates a current limited 3-phase-voltage directly from its galvanically separated DC-link. A sine filter smoothes this pulse width modulated voltage to provide a quasi-sinusoidal voltage waveform at the output terminals of the auxiliary converter. Two outputs are available, one with fixed and one with variable frequency for the fan of the cooling tower.



01

01 Electric multiple unit of the type FLIRT3 for Intercity PKP, Poland

02 Main Circuit of BORDLINE® CC1500 DC

### Powerful control platform

ABB traction converters are built on the AC 800PEC control platform, probably the most powerful modular controller for high-speed performance on the market. This control platform is also used in a wide range of other industrial applications. The AC 800PEC software is implemented on three performance levels, and this provides an excellent range of control and communication functionality in cycle times that extend from the sub-microsecond to the millisecond level. Compared to most other commercially available traction control systems, the modular application software in the AC 800PEC speeds up train commissioning significantly.

### Cooling system

The equipment is efficiently cooled using service water, allowing a very compact construction. The temperature of the coolant is lowered using an external heat exchanger.

### Mechanical design


BORDLINE® CC1500 DC is housed in a traction proven IP54 cabinet, designed for mounting in the machine room. The modular design allows an easy maintenance access.

ABB Switzerland Ltd  
Traction  
Austrasse  
5300 Turgi, Switzerland  
sales.traction@ch.abb.com

[abb.com/railway](http://abb.com/railway)  
[abb.com/tractionconverters](http://abb.com/tractionconverters)

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB AG does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

02



### Diagnostic and service

The service friendly modular design with standard components ensures high reliability and low life cycle costs for maintaining the system. The Compact Converter are delivered with BORDLINE® View, a diagnostic tool to visualize signals, parameter and state of traction system. It consists of an advanced self-diagnostic function, which gives advice and instructions for service and repair. BORDLINE® View is easy to use and runs on a standard PC.

### Application example

BORDLINE® CC1500 DC is mounted in Stadler's electric multiple unit of the type FLIRT3 for PKP Intercity, Poland. The traction solution is based on the well-proven 3kV traction converters in Stadler's FLIRT fleet in Poland and Italy.

Technical data	BORDLINE® CC1500 DC_3kV_M_1500
DC line voltage (EN 50163)	3 kVdc
Propulsion output	0...2200 Vac, 2 x 750 kW at wheel
Braking chopper	1400 kW
Auxiliary converter 1	3 x 400 V / 50 Hz, 210 kVA
Auxiliary converter 2	3 x 0...400 V / 0...50 Hz, 20 kVA
Battery charger (optional, replacing Aux 2)	24 / 36 / 72 /110 Vdc, 10 kW
Vehicle control interface	CANopen, I/Os
Dimensions (L x W x H)	1803 x 850 x 1900 mm
Weight	1700 kg

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB AG. Copyright© 2018 ABB All rights reserved