






SACE Tmax XT

RHD - Comando a maniglia rotante diretto Tmax XT7
RHD - Rotary handle operating mechanism direct Tmax XT7
RHD - Drehhebelantrieb direkt XT7
RHD - Commande par poignée rotative directe XT7
RHD - Mando giratorio directo XT7
RHD - 旋转手柄操作机构 XT7

XT7







2

XT7 F



XT7 W







3


XT7 F

XT7 W






7




8

XT7 F/W




9


XT7 F/W



10

XT7 F/W







12



XT7 F



XT7 W



13

XT7 F/W

Max 3, $\varnothing 5\sim 8\text{mm}$ Max 3, $\varnothing 0.2''\sim 0.31''$



	With flange con mostrina	Without flange senza mostrina
A	201 (7.91")	192 (7.67")
B	116 (4.56")	107 (4.21")
C	24.25 (0.95")	19.75 (0.77")

