

S = { Ø13 – Special IM 2001/*11
M10 – Special IM 2101/*11

M2AA 112
(* Except 112 MC

Additional information:

VC005: Metal protective roof, vertical motor, shaft down / Doble protector de ventilador


VC233: Flange ring FF 165 / Aro brida FF 165 // VC234: Flange ring FT 165 / Aro brida FT 165

Motor Dimension Print

Motor Type :
M2AA 112 (*)

Document N° :
3GZE 500 110-951.005

Description : **Motor foot and flange mounted special (2-pieces) IM2001/*11 or IM2101/*11**
Motor con patas y brida (2 piezas) IM2001/*11 o IM2101/*11



Unit : Discret Automation & Motion - Fábrica Motores
Date : 2012-12-12

Issued by : **ERM/ A. Caubera**
Approved by : **ERM/ G. Blanes**

Replaces :
Replaced by :

Asea Brown Boveri, S.A.

Customer Reference :

ABB