






ABB medium voltage drives Product overview




ABB medium voltage drives product overview



General purpose medium voltage drives			
Type	ACS 1000	ACS 2000	ACS 5000
Output voltage	2.3 / 3.3 / 4.0 / 4.16kV Optional: 6.0 / 6.6kV with step-up transformer	4.16kV 6.0 - 6.9kV	6.0–6.9kV Optional: 4.16 kV
Type of motor	Induction	Induction	Induction, synchronous or permanent magnet
Application type	General purpose	General purpose	General purpose
Converter cooling	Air (A) / Water (W)	Air (A)	Air (A)
Type of converter	VSI - Voltage Source Inverter	VSI - Voltage Source Inverter	VSI - Voltage Source Inverter
Typical applications	Pumps, fans, conveyors, extruders, mixers, compressors, grinding mills, suitable for retrofit of existing motors	Pumps, fans, conveyors, extruders, mixers, compressors, grinding mills, suitable for retrofit of existing motors	Compressors, extruders, pumps, fans, conveyors, gas turbine starters
Power range	Air: 400-2700 HP (315kW–2MW) Water: 2500-6700 HP (1.8–5MW)	300-2000 HP (250-1600kW)	Air: 1500-8000 HP (2–7MW)
Input selection	Diodes:12/24-pulse rectifier	High-voltage IGBTs:Active Front End (AFE) for operation with two-winding transformer or direct-to-line connection	Diodes:36-pulse rectifier
Output selection	IGCTs: 3-level VSI, sinusoidal output	High-voltage IGBTs: 5-level VSI, 9-level output waveform	IGCTs: 5-level VSI, 9-level output waveform
Maximum output frequency	66Hz (optional 82.5Hz)	75Hz	75Hz
Field weakening	> 45Hz (max. 1:1.5)	> 15Hz (max. 1:5)	> 35Hz (max. 1:2, higher optional)
Typical system diagram			
Speed-torque quadrants			
Special features and benefits	<ul style="list-style-type: none"> – Sinusoidal output – Constant network power factor over whole speed range – DTC (Direct Torque Control) – Fuseless 	<ul style="list-style-type: none"> – AFE for minimized harmonics – Direct-to-line connection – Constant network power factor over whole speed range – DTC (Direct Torque Control) – Fuseless 	<ul style="list-style-type: none"> – Constant network power factor over whole speed range – DTC (Direct Torque Control) – Fuseless
Examples of options	<ul style="list-style-type: none"> – Braking chopper – Synchronous bypass – Redundant cooling fan / pump – Integrated input transformer 	<ul style="list-style-type: none"> – Redundant cooling fan – Extended I/O for supervision functions – Regeneration 	<ul style="list-style-type: none"> – Synchronous bypass – Extended I/Os for supervision functions – Integrated input transformer – Redundant cooling fan



Special purpose medium voltage drives

ACS 5000	ACS 6000	MEGADRIVE-LCI
6.0–6.9kV Optional: 4.16 kV	3.0–3.3kV Optional: 2.3kV	2.1–10kV
Induction, synchronous or permanent magnet	Induction, synchronous or permanent magnet	Synchronous
Special purpose	Special purpose	Special purpose
Water (W)	Water (W)	Air (A) / Water (W)
VSI - Voltage Source Inverter	VSI - Voltage Source Inverter	LCI - Load Commutated Inverter
Compressors, extruders, pumps, fans, grinding mills, conveyors, blast furnace blowers	Rolling mills, marine propulsion, mine hoists, pumps, fans, compressors, grinding mills, extruders, conveyors	Compressors, pumps, fans, blast furnace blowers, pump storage plants
Water: 6800-43,000 HP (5–32MW) higher on request	4000-35,000 HP (3–27MW)	Air: 1500-40,000 HP (2–31MW) Water: 9000-100,000 HP (7–72MW) higher on request
Diodes:36-pulse rectifier	Diodes:12/24-pulse rectifier (LSU) or IGCT:Active rectifier (ARU)	Thyristors:6/12/24-pulse rectifier
IGCTs: 5-level VSI, 9-level output waveform	IGCTs: 3-level VSI, 5-level output waveform	Thyristors: 6/12-pulse inverter
75Hz (optional 250Hz)	75Hz (higher on request)	60Hz (optional 120Hz)
> 35Hz (max. 1:2, higher optional)	> 3Hz (max. 1:4.5)	Customized
		
		
<ul style="list-style-type: none"> Constant network power factor over whole speed range DTC (Direct Torque Control) Fuseless 	<ul style="list-style-type: none"> Constant network power factor over whole speed range Optimized pulse pattern to minimize network harmonics (with IGCT) DTC (Direct Torque Control) Multi-motor drive with common DC bus Fuseless 	<ul style="list-style-type: none"> Soft start of large synchronous motors and generators Fuseless
<ul style="list-style-type: none"> Synchronous bypass Extended I/Os for supervision functions Redundant cooling pump 	<ul style="list-style-type: none"> Reactive power compensation (ARU) Extended I/Os for supervision functions Braking chopper Customized 	Customized

Contact us

ABB Inc.

Medium Voltage Drives

16250 W. Glendale Drive

New Berlin, WI 53151

Tel: 800-752-0696

Fax: 262-785-3322

E-Mail: mv.drives.sales@us.abb.com

www.abb.us/drives

ABB (www.abb.us) is a leader in power and automation technologies that enable utility and industry customers to improve their performance while lowering environmental impact. ABB is the world's largest drives manufacturer. The ABB Group of companies operates in around 100 countries and employs more than 120,000 people.