

TECHNICAL DATA SHEET

Terminals, fork

Vinyl-insulated, DIN double crimp

Spec-Kon[®]

**Features:**

- Easy entry double crimp
- Corrosive resistant plating
- Color coded to wire size range

Maximum rating:

- 75°C Max
- 600 volts
- Copper conductors only

Application:

- ERG9004

Vinyl-insulated DIN fork terminals for wire termination of copper conductors ranging from 0.5mm² to 6mm²


Certifications / Standards:**Conforms to:**

- IEC 60352-2

Materials / Finishes:

- Copper terminal
- Electro-Tin plated
- Vinyl insulation

Terminals, fork:
Vinyl-insulated, DIN double crimp

Product selection										
Drawing	Part no:	Wire size range (mm ²)	Color	Stud hole size		Dimensions (mm)				Crimping tool
				d2	L	F	W	D		
	F1.5-3VDC-DIN	0.5 - 1.5	Red	M3	18.6	17.0	6.0	4.3	ERG9004	
	F1.5-35VDC-DIN	0.5 - 1.5	Red	M3.5	18.6	17.0	6.0	4.3		
	F1.5-4VDC-DIN	0.5 - 1.5	Red	M4	20.6	18.0	6.8	4.3		
	F1.5-5VDC-DIN	0.5 - 1.5	Red	M5	22.6	19.0	10.0	4.3		
	F1.5-6VDC-DIN	0.5 - 1.5	Red	M6	25.2	19.0	11.0	4.3		
	F2.5-3VDC-DIN	1.5 - 2.5	Blue	M3	18.6	17.0	5.5	4.8		
	F2.5-35VDC-DIN	1.5 - 2.5	Blue	M3.5	18.6	17.0	6.0	4.8		
	F2.5-4VDC-DIN	1.5 - 2.5	Blue	M4	20.6	18.0	6.8	4.8		
	F2.5-5VDC-DIN	1.5 - 2.5	Blue	M5	23.6	20.0	10.0	4.8		
	F2.5-6VDC-DIN	1.5 - 2.5	Blue	M6	26.2	22.0	11.0	4.8		
	F6-4VDC-DIN	4 - 6	Yellow	M4	24.2	21.0	8.0	6.7		
	F6-5VDC-DIN	4 - 6	Yellow	M5	26.4	22.0	10.0	6.7		
	F6-6VDC-DIN	4 - 6	Yellow	M6	28.2	23.0	11.0	6.7		
	F6-8VDC-DIN	4 - 6	Yellow	M8	32.6	26.0	14.0	6.7		
	F6-10VDC-DIN	4 - 6	Yellow	M10	35.6	28.0	18.0	6.7		

Note: Products must be installed in accordance with applicable national and local electrical codes.