

---

TECHNICAL DATA SHEET

# Terminals, fork

## Nylon-insulated, double crimp

### Spec-Kon<sup>®</sup>



---

**Features:**

- Easy entry double crimp
- Corrosive resistant plating
- Color coded to wire size range

---

**Maximum rating:**

- 105°C Max
- 600 volts
- Copper conductors only

---

**Application tool:**

- ERG9004

Nylon-insulated fork terminals for wire termination of copper conductors ranging from 0.5mm<sup>2</sup> to 6mm<sup>2</sup>

**Certifications / Standards:**



---

**Conforms to:**


- IEC 60352-2

---

**Materials / Finishes:**

- Copper terminal
- Electro-Tin plated
- Nylon insulation

**Terminals, fork:**  
Nylon-insulated, double crimp

Product selection										
Drawing	Part no:	Wire size range (mm <sup>2</sup> )	Color	Stud hole size		Dimensions (mm)				Crimping tool
				d2	L	F	W	D		
	F1.5-3NDC	0.5 - 1.5	Red	M3	21.7	6.5	5.7	4.4	ERG9004	
	F1.5-35NDC	0.5 - 1.5	Red	M3.5	21.7	6.5	6.4	4.4		
	F1.5-4NDC	0.5 - 1.5	Red	M4	21.7	6.5	8.1	4.4		
	F1.5-5NDC	0.5 - 1.5	Red	M5	21.7	6.5	9.5	4.4		
	F1.5-6NDC	0.5 - 1.5	Red	M6	27.7	11.0	12.0	4.4		
	F2.5-3NDC	1.5 - 2.5	Blue	M3	21.7	6.5	5.7	5.0		
	F2.5-35NDC	1.5 - 2.5	Blue	M3.5	21.7	6.5	6.4	5.0		
	F2.5-4NDC	1.5 - 2.5	Blue	M4	21.7	6.5	8.1	5.0		
	F2.5-5NDC	1.5 - 2.5	Blue	M5	21.7	6.5	9.3	5.0		
	F2.5-6NDC	1.5 - 2.5	Blue	M6	27.7	11.0	12.0	5.0		
	F6-35NDC	4.0-6.0	Yellow	M3.5	25.2	7.0	8.3	7.0		
	F6-4NDC	4.0-6.0	Yellow	M4	25.2	7.0	9.0	7.0		
	F6-5NDC	4.0-6.0	Yellow	M5	25.2	7.0	9.0	7.0		
	F6-6NDC	4.0-6.0	Yellow	M6	31.2	12.0	12.0	7.0		
	F6-8NDC	4.0-6.0	Yellow	M8	30.2	11.5	14.0	7.0		

Note: Products must be installed in accordance with applicable national and local electrical codes.