

USER GUIDE

MAN0124 rev 5

MATRIX Series



Style conventions used in this document:

UI Text: Text that represents elements of the UI such as button names, menu options etc. is presented with a grey background and border, in Tahoma font which is traditionally used in Windows UIs. For example:

Ok

Standard Terms (Jargon): Text that is not English Language but instead refers to industry standard concepts such as Strategy, BACnet, or Analog Input is represents in slightly condensed font. For example:

BACnet

Code: Text that represents File paths, Code snippets or text file configuration settings is presented in fixed-width font, with a grey background and border. For example:

```
$config_file = c:\CYLON\settings\config.txt
```

Parameter values: Text that represents values to be entered into UI fields or displayed in dialogs is represented in fixed-width font with a shaded background. For example

10°C

Product Names: Text that represents a product name is represented in bold colored text. For example

INTEGRA™

Company Brand names: Brands that are not product names are represented by bold slightly compressed text:

ABB Active Energy

PC Keyboard keys: Text representing an instruction to press a particular key on the keyboard is enclosed in square brackets and in bold font. For example:

[Ctrl]+[1]

table of contents

1	MATRIX SERIES INTRODUCTION	
	Tools Required.....	4
	SAFETY PRECAUTIONS	4
	STATIC DISCHARGE PRECAUTIONS	4
	MISCELLANEOUS PRECAUTIONS	4
2	PRODUCT MOUNTING	
	Enclosure Cover.....	5
3	HARDWARE LAYOUT	
	Power Requirements	7
	Led Indication	7
4	COMMUNICATION CONNECTIONS	
	Ethernet Network	8
	Cable Type and Length.....	8
	EIA-485 Network	9
	Connecting EIA-485 Networks	9
	Network Termination and Biasing	9
	LED Indication	10
5	PRODUCT SPECIFICATIONS	
	EIA-485 Connections	11
	Ethernet Connection.....	11
	Product Setup and Configuration.....	11
	CPU	11
	Power Requirements	11
	Operating Conditions	11
	Agency Approvals	11

1 MATRIX Series Introduction

The following document provides general information relative to the hardware installation of the **MATRIX Series** Area Controller hardware. Please read through this document carefully before proceeding with the hardware installation process.

Unpack your Aspect MATRIX Series Area Controller and inspect the contents for damaged or missing items. Included in this package, you should find the following items:

- MATRIX Series Area Controller
- MATRIX Series Controller Hardware Installation Guide (this document)

Tools Required

The following tools and supply may be required for installation:

- Small flat-bladed screwdriver - for field-bus and power connectors
- Drill - for mounting the product onto a wall
- Wire-strippers - for terminating EIA-485 connections

SAFETY PRECAUTIONS

Note: All equipment must be installed in accordance with NEC and local codes. For more information on local codes, please check state/local regulations in your area.

Caution: To prevent damage to any of the electrical components of this product and to ensure that it continually operates, do not attempt to alter any componentry.

STATIC DISCHARGE PRECAUTIONS

WARNING: Follow the precautions provided specific to static discharge.

Static discharge can produce voltages high enough to damage electronic circuits and components. The microprocessor and associated circuitry are sensitive to static discharge. Follow these precautions while working with the product during service and installation:

Work in a static-free environments

Discharge any static electricity you may have accumulated by touching a known, securely grounded object.

Do not handle the printed circuit board (PCB) without proper protection against static discharge. Users should handle PCB components while wearing a ground bracelet or strap (connected to Earth ground).

MISCELLANEOUS PRECAUTIONS


Note: Do not apply this product to aerospace systems, mainline communication systems, nuclear power control systems or medical equipment involved in life support that require high reliability and safety, as it is not intended for such use or application.

Note: This device complies with Part 15 of the FCC rules. Operation of this equipment is subject to the following conditions:

1. This device may not cause harmful interference.
2. This device must accept any interference received, including interference that may cause undesired operation.


2 Product Mounting

The Aspect MATRIX Series Area Controller ships with an approved enclosure consistent with most electrical standards and regulations. It is intended for indoor applications only and should be installed in a location that is dry, away from direct sunlight and free from excessive dust, vibration, and electrical interference. Mount the product in a location that allows clearance for ease of wiring and service. Use the two keyhole-style screw holes located on the back of the enclosure for assistance with mounting. The product is capable of being mounted on a DIN rail by installing the provided mounting bracket.



ENCLOSURE COVER

The enclosure cover of the product is designed to be removed for servicing the device. The cover is removed by unscrewing the single screw in the cover then lifting the cover away from the base as shown. Care should be taken when removing the cover on a mounted unit to prevent it from being dropped and damaging the cover.



3 Hardware Layout

Below is an illustration of the hardware layout of the product. The device includes connection ports for Main Power, EIA-485 network connectivity and Ethernet connectivity. Depending on the model of MATRIX Series Area Controller you have purchased, your application may involve using one of the or both EIA-485 network ports.




Figure 1-4 - Aspect MATRIX Series Area Controller Board Layout

POWER REQUIREMENTS

This product requires a transformer capable of providing 24VAC power to the product. Use of a UL listed 24VAC transformer is recommended.

To connect power, use the supplied two-position terminal plug. The output leads from the transformer should be connected to the terminal plug. The terminal plug is then connected into the socket marked J1 on the PCB. American Auto-Matrix recommends using 18AWG cable for power wiring.




Figure 1-5 Connecting Power to MATRIX Series Area Controller

WARNING: Do not share the power source for Aspect MATRIX Series MAX Area Controller with other devices. Damage to the product as a result of improper power and wiring will void product warranty.

LED INDICATION

The PCB of the product includes diagnostic LEDs, providing user feedback when power has been connected to the device. When power is connected, all three of the LEDs should be illuminated. The power diagnostic LEDs are located near port 1's terminal block switches.




Figure 1-6 Power LEDs on Aspect MATRIX Series Area Controller PCB

4 Communication Connections

Communication connections should be made with care. To avoid conflicts with existing networks, it is recommended all communication configuration of the product be performed prior to connecting physical media from the building automation system. Refer to Aspect Studio On-Line Help System for additional information.

Caution: It is recommended that all software configuration be performed prior to physically connecting this to any associated communication product networks.

ETHERNET NETWORK

Ethernet is a high-speed network layer widely used in commercial buildings. This product includes an on-board Ethernet adapter, allowing users communicate with the device for product setup, as well as for building automation routines and applications. The Ethernet network interface is located on the single board computer card.

The on-board Ethernet network interface supports 10Base-T (10Mbps) and 100Base-T (100Mbps) Ethernet connections. The product will automatically switch to 100Base-T operations if other devices and cabling connected to the same subnetwork support this

CABLE TYPE AND LENGTH

Use an approved Category 5 (CAT5) Ethernet patch cable with RJ-45 plugs to connect the product to an Ethernet switch or hub. Use professionally manufactured cables to assure reliable transmission rates and connectivity between devices. Category 5 wiring is typically limited to about 100 meters (320 feet).




Figure 1-7 Standard Ethernet Connection Pinout

EIA-485 NETWORK

The EIA-485 network ports are used to accommodate serial network protocols that utilize two-wire, shielded-twisted pair cabling - such as BACnet MS/TP, American Auto-Matrix PUP, and Modbus RTU. Terminals for EIA-485 network connections are located on the left side of the controller board and are labeled J2 and J3. Each terminal has a connection for Network Positive (N+), Network Negative (N-), and Signal Ground Reference Wire (SG, commonly used for serial networks that utilize a reference wire for electrical stability).

The Matrix Area Controller should be installed at an electrical end of the EIA-485 network. Avoid network topologies where the network is “t-tapped” or “starred”.

CONNECTING EIA-485 NETWORKS

Connect the serial network to the determined EIA-485 port. Be sure to maintain network polarity at all times. Failure to do so can result in loss of network communications. For protection against ground loops or noise, connect the drain wire of the 485 network wire to a reliable earth ground.




Figure 1-8 MS/TP Network Connection

NETWORK TERMINATION AND BIASING

Adjacent to each EIA-485 port is a two-position switch block, which applies termination and biasing to your 485 network. To enable either termination (TERM) or biasing (BIAS), configure the respective switch towards the ON (Up) position.

When applying termination, be certain that it is applied at both ends of your EIA-485 network at the two end devices. In termination applications, biasing should also be enabled to ensure proper idle state voltage.




Figure 1-9 Termination and Biasing Switches and LED Indicators

LED INDICATION

Located below the network termination and biasing switches is a set of diagnostic LEDs that can be useful for troubleshooting network communication problems.



Figure 1-10 Network Diagnostic LEDs

Table 1-1: EIA-485 LED Diagnostics

LED Position	Notes
TXD	This LED will flash anytime data is transmitted by the Matrix Area Controller to the field bus network. On an active network, this light should flash anytime the device passes a network token to another device or routes a request made by another device.
RXD	This LED will flash anytime data is received by the Matrix Area Controller from the field bus network. On an active network, this light should flash anytime there is activity on the network.
PERR	This LED will flash upon the event a parity error occurs on the network. A parity error is caused by a mismatch between the calculated checksum and value received with the packet. The most common reason for a packet error is if more than one unit is attempting to communicate on the network at once, indicating the presence of a duplicate token or duplicate address.
BERR	This LED will flash upon the event a byte error occurs on the field bus network. A byte error is caused when information is lost during network communications, and is detected in the start, stop, or data bit timings. The most common reason for a byte error is due to devices attempting to communicate on the network at different baud rates.

Note: This product utilizes native EIA-485 communication drivers. Therefore, all network communications to field-devices should occur over specified network media as outlined in American Auto-Matrix product documentation. The use of media converters (such as Serial-to-Ethernet modems) not certified or sold by AAM is discouraged.

5 Product Specifications

EIA-485 CONNECTIONS

Connection Type: 3 position

Termination Count: model dependent, up to 2 connections

Serial: EIA-485

Baud Rates Supported: 9.6kbps, 19.2kbps, 38.4kbps, 57.6kbps, 76.8kbps, 115.2kbps

Data isolation: GMR Data Isolated

Termination: 249 Ohm, switchselectable

Biasing: 3.32k, switch selectable

LED: indication for TXD, RXD, Byte-Error, Parity-Error

Protocol: license enforced, driverselectable

Network Load: license enforced, up to 64 devices per port, license restrictions apply

ETHERNET CONNECTION

Termination Count: 1connection

Connection Type: RJ-45, female

Speed: 10/100Mb auto-sensing

PRODUCT SETUP AND CONFIGURATION

Software: ASPECT-Studio with USB Copy Protection Key and License File

Browser: Windows Internet Explorer v7.0 or later, Mozilla Firefox v3.0 or later, Apple Safari v3.2 or later, Google Chrome v1.0 or later

CPU

Processor: ARM Cortex-A8 1 Ghz

Memory: 512MB RAM, 2 GB Flash

POWER REQUIREMENTS

Connection: 2 position

Power Source: 24 VAC, 50/60Hz, 2.7A max

OPERATING CONDITIONS

Temperature: 32-104°F (0- 40°C) ambient

Humidity: 0-80%, non-condensing

Altitude: -2000 to + 10,000 ft. (-650 to +3500m)

AGENCY APPROVALS

CE Approved

FCC, Class A Computing Device; Part 15

UL listed 916, Management Equipment, Energy (PAZX)



—
ABB CYLON CONTROLS

Clonsaugh Business &
Technology Park
Clonsaugh
Dublin 17
Ireland

Tel.: +353 1 245 0500
Fax: +353 1 245 0501
Email: info@cylon.com

—
ABB CYLON CONTROLS

ONE TECHNOLOGY LANE
EXPORT,
PA 15632

Tel.: +1 724 733-2000
Fax: +1 724 327-6124