

PRODUCT SHEET

OMC1

Muting connection box

OMC1 is a connection box that simplifies the connection of muting sensors to a light guard.

Using fast and simple M12 connectors, 2 or 4 muting sensors can easily be connected.

With an IP67 rating, OMC1 can be used in most field applications.



Easy to install

The M12 connectors speed up the connection and reduce the risk of connection error.



Reliable in extreme environment

The IP67 housing makes OMC1 suitable for most field applications.

Ordering information

OMC1



OMC1

2TLC172018V0201



M12-CYMUTE

2TLC172014V0201



M12-C112

2TLC172049F0201



M12-C203

2TLC172039F0201

Ordering details

Description	Type	Order code
Connection box for two or four muting sensors	OMC1	2TLA022316R2000

Muting cable (between light guard and OMC1)


Type of detection	Light guard	Type	Order code
Finger (14 mm resolution)	Orion1-4-14-zzz-E	M12-C02PT62RM	2TLA022315R0300
Hand (30 mm resolution)	Orion1-4-30-zzz-E	M12-C02PT62RM	2TLA022315R0300
Body up to 50 m, two sides connection	Orion2-4-Kx-zzz-E	M12-CYMUTE	2TLA022316R0100
Body up to 8 m, one side connection	Orion3-4-KxC-zzz-E Orion3-4-M1C-zzz	M12-CYMUTE	2TLA022316R0100

Cables

Description	Type	Order code	OMC1 to Mute R2	M12-CYMUTE to el-cabinet	M12-C02PT62RM to el-cabinet
M12-5 male + female connectors with 1 m shielded cable	M12-C112	2TLA020056R2000	X		
M12-5 male + female connectors with 3 m shielded cable	M12-C312	2TLA020056R2100	X		
M12-5 male + female connectors with 6 m shielded cable	M12-C612	2TLA020056R2200	X		
M12-5 male + female connectors with 10 m shielded cable	M12-C1012	2TLA020056R2300	X		
M12-5 male + female connectors with 20 m shielded cable	M12-C2012	2TLA020056R2400	X		
Straight M12-8 female connector with 6 m shielded cable	M12-C63	2TLA020056R3000		X	
Straight M12-8 female connector with 10 m shielded cable	M12-C103	2TLA020056R4000		X	
Straight M12-8 female connector with 20 m shielded cable	M12-C203	2TLA020056R4100		X	
Straight M12-12 female connector with 6 m shielded cable	M12-C65	2TLA020056R7200			X
Straight M12-12 female connector with 10 m shielded cable	M12-C105	2TLA020056R7300			X
Straight M12-12 female connector with 20 m shielded cable	M12-C205	2TLA020056R7500			X

Technical data

OMC1



—
All dimensions in mm

Technical data

Power supply

Voltage Min: 10 V, max +30 V

Mechanical data

Color Black

Material PBT

Size 118 x 54 x 28 (L x W x H) mm

Weight 160 g

Protection class IP67

Connectors 5 x M12-5 pole female connector


Environmental data

Ambient temperature -25...+80°C

Humidity range 35 to 85% (with no icing or condensation)


Connection examples

Connection of OMC1 with M12-CYMUTE and the muting sensors




Orion2 Extended or Orion3 Extended, muting cable M12-CYMUTE and OMC1.
NB: M12-5 pole cable shall be used between muting sensors and OMC1 inputs A1, B1, A2, B2.

Electrical connection



You will find information about the muting function in respective Orion manual.



- 1: +24 VDC
- 2: Muting B
- 3: 0V
- 4: Muting A
- 5: Not connected

Note

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents - in whole or in parts - is forbidden without prior written consent of ABB.

Copyright© 2019 ABB
All rights reserved

ABB AB

Jokab Safety

Varlabergsvägen 11
SE-434 39 Kungsbacka
Tel. +46 (0) 21-32 50 00

www.abb.com/jokabsafety

