



MIDWEST ELECTRIC PRODUCTS INC.
305 Gregson Drive Cary, NC 27511

Instruction Bulletin (IBUL)	Drawing: MEPI80
Page 1 of 1	CN: C094002
Subject:	Revision: 03
Customer instruction for C-64-U angle caps	Created: 02/26/2002

The following is the customer instruction for wiring the C-64-U angle cap.

C-64-U
ANGLE CAP

WIRING INSTRUCTION

NOTICE: Connect only copper or copper clad wire to this device. Cord type: S, SJ, SJO, SO, ST, STO. Wire Size #4 through #10 AWG.

1. Strip outer insulation back 3 inches.
2. Cut red and black wire to 1-7/8 inches long; white wire 1 inch long.
3. Strip green and white wires back 3/4 inch; black and red wires back 5/8 inch.
4. Remove cap cover. Raise contact blades about 3/4 inch or just enough to insert wires into clamps. Tighten clamp screws to a torque of 20-25 inch pounds.
5. Screw down cord clamp using (2) 7/8-#8 screws and fasten cover securely with (3) 1-1/4-inch-long #4 screws.

MIDWEST ELECTRIC PRODUCTS, INC.
MEPI80 Cary, NC