


On-load tap-changer type UCGL./C, VUCGL./C, 9 tap positions, linear switching.
 Min. effective No. of turns in pos. 1.
 The tap-changer is delivered set in pos. 5, the preceding pos. was 4.

Lindningskopplare typ UCGL./C, VUCGL./C, 9 lägen, linjär koppling.
 Min antal effektiva varv i läge 1.
 Lindningskopplaren levereras inställd i läge 5, föregående läge var 4.

Pos. Läge	Tap selector and diverter switch connect Väljaren och lastkopplaren förbinder
1	1-V-x
2	2-H-v
3	3-V-x
4	4-H-v
5	5-V-x
6	6-H-v
7	7-V-x
8	8-H-v
9	9-V-x



We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden.
 © ABB 19

The tap-changer is shown in pos. 5, the preceding pos. was 4.
 The tap selector is seen from above.
 Contact arm V is located above contact arm H.

Lindningskopplaren visad i läge 5, föregående läge var 4.
 Väljaren sedd uppifrån.
 Kontaktarm V ligger över kontaktarm H.

Continuous lines show leads included in the tap-changer. Dashed lines show leads belonging to the cleats and leads.

Heldragna linjer visar ledare som ingår i lindningskopplaren. Streckade linjer visar ledare som tillhör anslutningsdonet.

Sheet	Cont		
	Year	Week	
Form No.	Dept		
	RevInd	Revision	Appd Year Week
Design checked by	Accepted by qual control	Accepted for prod by	Description (English)
	R.Yngvesson		CONNECTION DIAGRAM
Design checked by	Design checked by	Drawn by	Description (own language)
	B-O.Stenestam	L.Bergman	KOPPLINGSSHEMA
Design checked by	Drawing checked by	Issued by Dept Year Week	Lang Sheet
	M.Hedlund	COM/TKO 97 22	1
Asea Brown Boveri			File name 0376-5
5492 0376-5			RevInd Cont -