


Temp.
0 25 40 50 60



Shift index for long-time delay only.

MULTIPLES OF CURRENT RATING



Industrial Solutions

Molded Case Circuit Breaker E 100 LINE

Type TEB, 60-80 Amperes
Enclosure Compensated
Long-time Delay and Instantaneous
Time-current Curves
Curves show enclosure-compensated circuit breaker in open air, 40°C ambient, wired with conductors of corresponding rating, no prior load. For all other ambients, use shift index at top of sheet.

GES6123

Adjustments
Long-time delay thermal trip: not adjustable.
Instantaneous magnetic trip: not adjustable.

Current Ratings

60, 70 and 80 Amperes

Voltage Ratings

1 pole – 120 Vac (125 Vdc)
2 and 3 pole – 240 Vac (250 Vdc)

Frequency Rating

60 Hertz

by ABB

GE is a registered trademark used under license from General Electric Company