



Test Report				Date of issue: 5.6.2014							
				Serial No.: 75033778003001B							
				Type: M3JP 355SMB 8 IMB3/IM1001							
				Product Code: 3GJP354220-ADG							
				Protection type: Ex d IIB T4 Gb							
				Cert. No.: LCIE 10 ATEX 3089X / IECEx LCI 04.0008X							
Rating:				V	Hz	kW	r/min	A	cos φ	Duty	
3~Motor				400	D	50	150,0	744	287	0,79	S1
Insul.cl.F				690	Y	50	150,0	744	166	0,79	S1
IP55				415	D	50	150,0	745	276	0,79	S1
400 V 50Hz: 95,5(100%) - 95,4(75%) - 95,0(50%)											
Resistance Line				Ambient: 17,0 °C				Insulation resistance at 17,0 °C		Overload	
U <sub>1</sub> - V <sub>1</sub>				0,01429 Ω				R > 2000 Mohm		1000 V	
U <sub>1</sub> - W <sub>1</sub>				0,01430 Ω						Voltage 130 % 180s	
V <sub>1</sub> - W <sub>1</sub>				0,01430 Ω						Torque 160 % 15s	
								High-voltage test winding		2400 V 60 s	
Test	Torque [Nm]	Line U[V]	f[Hz]	Input I[A]	P1 [kW]	Output P2 [kW]	n[r/min]	cos φ	η [%]		
No load test		400,3 D	50	129,8	2,80		750	0,03			
Locked rotor test		81,7 D	50	288,4	8,20		0	0,20			
Thermal test ( 100% load )	1925,8	400 D	50	292,8	157,08	150,00	744	0,77	95,50		
Partial load points:											
~75% load	1441,8	400 D	50	235,3	117,90	112,50	745	0,72	95,40		
~50% load	958,4	400 D	50	184,8	78,92	75,00	747	0,62	95,00		
~25% load	478,5	400 D	50	146,6	40,64	37,50	748	0,40	92,30		
Temperature rise at rated load.				[°C]		[K]	Method		Measurement method		
Stator winding :						53,3	1		1 Resistance		
Frame :						21,9	2		2 Thermometer		
Bearing D-end :						32,2	2		3 Thermocouples		
Ambient Temperature :				25			2				
Manufactured and tested in accordance with rules of IEC 60034-1 and IEC 60034-2-1.											
PLL determined from residual loss.											
On behalf of customer											
On behalf of manufacturer				Date of test				3.12.2011			
Tested by ABB Shanghai Motors , LV Motors, Shanghai,P.R.China								Telephone		+86 21 54723133	
								Telefax		+86 21 54725009	

Computer print-out valid without signature.