


Data Sheet 10/41-1.15-EN

Multipoint Recorder PointMaster 100

Consumables and accessories

Ordering information						
	Catalog Number	Code				
Scale	0318142V-					
Character size for 1 graduation: 6 mm; for 2 graduations: 5 mm Character size for 3, 4, 5, 6 graduations: 2 mm						
1st graduation		3	1			
2nd graduation		3	2			
3rd graduation		3	3			
4th graduation		3	4			
5th graduation		3	5			
6th graduation		3	6			
Without graduation (start and end marked)				0		
Graduation 0...100				1		
Graduation as specified (clear text)				3		
Ruler	1882230V-					
Graduation as specified (clear text)		3	5	0		
Tag name plate	0319797V-					
(Character height 3 mm, max. 31 characters per channel)						
Labelling as specified						
for measuring channel 1 (clear text)		5	7	2		
for measuring channel 2 (clear text)		5	7	5		
for measuring channel 3 (clear text)		5	7	8		
for measuring channel 4 (clear text)		5	8	1		
for measuring channel 5 (clear text)		5	8	4		
for measuring channel 6 (clear text)		5	8	7		

The three-digit Code-Numbers should be appended to the Catalog Number - separated by a slash



Multipoint Recorder PointMaster 100

Consumables and Accessories

10/41-1.15 EN

Ordering information				
	Catalog Number			
PARAPOINT 100 parameter definition program¹⁾	41495-3601084			
Adapter set²⁾	43083-0745566			
Bag with bus terminal resistors R ₁₁ = 390 Ω; R ₁₂ = 390 Ω; R ₁₃ = 150 Ω	43483-0319229			
Plug-in current divider for measuring ranges				
0...0.5 mA	43483-0318467			
0...2.5 mA	43483-0318468			
0...5 mA	43483-0318469			
0...100 mA	43483-0318470			
0...500 mA	43483-0318471			
Plug-in voltage divider for measuring ranges				
0...5 V	43483-0318472			
0...25 V	43483-0318473			
0...50 V	43483-0318474			
Ink head	41081-0318333			

¹⁾ User guidance in German, English and French

Hardware preconditions:

Processor	80486 or higher
Operating system	Windows version 3.1x or Win 95/98
Free working memory, min.	4 MByte RAM
Free memory on harddisc, min.	3 MByte
Diskette drive 3.5 inch.	storage density 1.44 MByte for installation (diskette operation not possible)
For graphics mode	VGA or better
Mouse	required
Serial interface	RS 232 or RS 485 to COM 1/2/3/4

²⁾ Consisting of:

- RS 232/RS 485 adapter
- Mains unit to RS 232/RS 485 adapter
- Connection cable (3 m), with plugs at both ends
- Adapter 9-pin to 25-pin

Contact us

ABB Ltd.

Process Automation

Howard Road, St. Neots
Cambridgeshire, PE19 8EU
UK

Phone: +44 (0)1480 475321

Fax: +44 (0)1480 217948

ABB Inc.

Process Automation

125 E. County Line Road
Warminster PA 18974
USA

Phone: +1 215 674 6000

Fax: +1 215 674 7183

ABB Automation Products GmbH

Process Automation

Borsigstr. 2
63755 Alzenau
Germany

Phone: +49 551 905-534

Fax: +49 551 905-555

www.abb.com

Note

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB.

Copyright© 2011 ABB

All rights reserved

3KXR091100R1001

10/41-1,15-EN 01.2011