



ABB PROPRIETARY AND CONFIDENTIAL INFORMATION
The information contained in the document has to be kept strictly confidential.
Any unauthorized use, reproduction, distribution or disclosure to third parties is strictly forbidden.
ABB reserves all rights regarding Intellectual Property Rights.
Copyright 2018 ABB. All rights reserved



- NOTE:**
1. 1/2-13 BOLT TYP. FOR FUSE CONNECTIONS SUPPLIED WITH SWITCH.
 2. ALL OUTLINE DIMENSIONS ARE SAME FOR MANUALLY AND ELECTRICALLY OPERATED DEVICES.
 3. DIMENSIONS ARE IN INCHES[MILLIMETERS].
 4. SEE USER'S GUIDE DEH-41689.
 5. CROSS REFERENCE TO ROTARY T-HANDLE THPC OUTLINE 139C41145H1&2.
 6. MATCHES DEPTH OF ROTARY T-HANDLE THPC SWITCH.
 7. REAR MOUNTED COOLING FINS ARE SHIPPED LOOSE AND MUST BE MOUNTED DURING HPC SWITCH INSTALLATION.
 8. CUT-OUT BASED ON USE OF TRIM PLATE .

DRAWING FILE 10112083P5		MODEL FILE 10112083G5					
DATE MODIFIED 10-Oct-20 08:50:17 AM		DESIGNED BY FIROZ					
Calculated for: VOLUME --		C/N# C095496		APPROVED BY RYAN SPARROW		TITLE OUTLINE - 200A, TOP FEED HPC SWITCH THPC23620T	
							
MASS --		MATERIAL SPECIFICATION --		FINISH SPECIFICATION --		UNITS in	LOCAL TITLE --
UNLESS OTHERWISE SPECIFIED		MATERIAL DESCRIPTION --		SIZE D	ROOT NUMBER 10112083	REV 3.5	RELEASE STATE Released
TOLERANCE ON: 1 PL DECIMALS ± 0.0 2 PL DECIMALS ± 0.02 3 PL DECIMALS ± 0.006 ANGLES ± 1.0		FINISH DESCRIPTION --		SCALE 1:5	PRODUCT LINE HPC		SHEET 1 of 1

