


On-load tap-changer type UBBL, 14 tap positions, linear switching.  
 Max effective No. of turns in pos 1.  
 The tap-changer is delivered set in pos 7.

Lindningskopplare typ UBBL, 14 lägen, linjär-koppling.  
 Max antal effektiva varv i läge 1.  
 Lindningskopplaren levereras inställd i läge 7.

Pos Läge	H connects förbinder
1	1 - 15
2	2 - 15
3	3 - 15
4	4 - 15
5	5 - 15
6	6 - 15
7	7 - 15
8	8 - 15
9	9 - 15
10	10 - 15
11	11 - 15
12	12 - 15
13	13 - 15
14	14 - 15

We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden. © ABB 19



1) OUTPUT TERMINAL  
STRÖMAVTAGNING

1) Internal connections between the terminals 15 of the three phases are included in the star-point type. Dashed lines show leads belonging to the cleats and leads.

Inre förbindningar mellan uttag 15 i de tre faserna ingår i nollpunktsutförande. Streckade linjer visar ledare som tillhör anslutningsdonet.

H Main contact  
Huvudkontakt  
M1, M2 Transition contacts  
Motståndskontakter

Rev Ind	Revision	Appd	Year	Week
-	-	-	-	-

Accepted by qual control	Accepted for prod by	Description (English)	DATAORIGINAL
R. Yngvesson		CONNECTION DIAGRAM UBBL	
Design checked by	Drawn by	Description (own language)	File name
B-O. Stenestam	L. Bergman	KOPPLINGSSCHEMA UBBL	0387-10
Drawing checked by	Issued by Dept	Year	Week
M. Hedlund	COM/TKO	97	32
<b>ABB</b> Asea Brown Boveri		5492 0387-10	
Lang	Sheet	Rev Ind	Cont
	1	-	-