



S = $\begin{cases} \text{Ø10} - \text{Special IM 2001/*11} \\ \text{M8} - \text{Special IM 2101/*11} \end{cases}$

M2AA 080

Additional information:

VC005: Metal protective roof, vertical motor, shaft down / Doble protector de ventilador

VC223: Flange ring FF 115 / Aro brida FF 115 // VC224: Flange ring FT 115 / Aro brida FT 115

| | | | |
|--|----------------------|---------------------------------|---------------------------------------|
| Motor Dimension Print | | Motor Type : M2AA 080 | Document Nº : 3GZE 500 080-931.005 |
| Description : Motor foot and flange mounted special (2-pieces) IM2001/*11 or IM2101/*11 Motor con patas y brida (2 piezas) IM2001/*11 o IM2101/*11 | | | |
| Unit : Discret Automation & Motion - Fábrica Motores | Date : 2012-11-29 | Issued by : ERM/ A. Caubera | Replaces : |
| | | Approved by : ERM/ G. Blanes | Replaced by : |
| Asea Brown Boveri, S.A. | Customer Reference : | | ABB |