

## M2AA 090

(\* Except 090\_LD

### Additional information:

VC005: Metal protective roof, vertical motor, shaft down / Doble protector de ventilador


VC218: Flange ring FT 85 / Aro brida FT 85

### Motor Dimension Print

Motor Type :  
M2AA 090 (\*)

Document N° :  
3GZE 500 090-911.005

Description : Motor foot and flange mounted special (2-pieces) IM2101/\*11  
Motor con patas y brida (2 piezas) IM2101/\*11



Unit : Discret Automation & Motion - Fábrica Motores  
Date : 2012-12-03

Issued by : ERM/ A. Caubera  
Approved by : ERM/ G. Blanes

Replaces :  
Replaced by :

Asea Brown Boveri, S.A.

Customer Reference :

**ABB**