

- **Ideal for small samples**
- **Thin probe allows use in test-tubes and cuvettes**
- **Grooved cap for safe grip**
- **Easily refillable**


Dimensions:	Stem length below cap	–	120mm
	Stem diameter	–	12mm
	Tip diameter	–	5mm
	Cap length	–	44mm
	Cap diameter	–	18mm

Reference Electrolyte: 3.5M KCl saturated with AgCl
(Order Code 1431-241)

pH Range: 0 - 14

Temperature Range: 0 - 100°C

Applications: Laboratory Combination Electrode for use in test-tubes, cuvettes and other small vessels. pH can be measured in samples as small as 0.5ml. However, the large electrolyte reservoir eliminates frequent refilling. Fitted with grooved cap for good grip, and integral replaceable refill stopper.



Electrode Range:	1416-000	Detachable cable type.
	1416-200	1 metre cable with coaxial connector
	1416-400	1 metre cable with BNC connector

Other connector types such as DIN are also available as options on detachable cables. With the appropriate cable the electrode will work with any other manufacturer's meter. Consult Cables List for details.

ABB Kent-Taylor is a British company with UK production sites at St Neots, Cambridgeshire and at Stonehouse, Gloucestershire. Other production sites are located at Lenno in Italy and Rochester in the United States. We are part of the Asea Brown-Boveri group which has worldwide sales of around £15 billion.

We are a specialist in measurement, manufacturing a wide range of sensors, including pH electrodes, ion-selective electrodes, Redox electrodes and oxygen sensors for a variety of applications ranging from Chemical processing to Pharmaceuticals.

We can bring over 40 years experience in the design and manufacture of Electro-chemical sensors to bear on pH and Chemical measurement applications and the quality of our products is assured by adherence to the ISO 9001 Standard.

The ABB Kent-Taylor range of pH, Redox and ion selective electrodes are designed to cover most common laboratory applications, these include:

- 1411 Series glass combination electrodes – for general laboratory use
- 1412 Series glass combination electrodes – for pure waters or low conductivity samples
- 1413 Series epoxy bodied combination electrodes – for general laboratory use

Plus many other specialist types, see our general laboratory electrode brochure.

Plus ion selective electrodes for the measurement of:

Sodium, Potassium, Ammonium, Chloride, Fluoride, Nitrate, Silver, Sulphide, Cyanide, Ammonia, Sulphur Dioxide and Dissolved Oxygen.

For further information please contact your local distributor or our sales office at Stonehouse.



The Company's policy is one of continuous product improvement and the right is reserved to modify the information contained herein without notice.
© ABB 1998 Printed in U.K. (1.98)

ABB Kent-Taylor Ltd.
Analytical & Flow Group
Stonehouse, Glos.
England, GL10 3TA
Tel: +44 (0) 1453 826661
Fax: +44 (0) 1453 827856

ABB Kent-Taylor Ltd.
St. Neots
Cambs.
England, PE19 3EU
Tel: +44 (0) 1480 475321
Fax: +44 (0) 1480 217948