





TYPE	TRANSITION	LEVEL	PART NO.
ZTX	OPEN	2	OXAM11-L2
ZTG	OPEN	3	OXAM11-L3
ZTGD	DELAYED	3	OXBM11-L3

NOTES



1. ENCLOSURE : NEMA TYPE1, WALL MOUNT.
2. MATERIAL:14 GA (.0747) 1018 HRS REF.
3. FINISH : ANSI 61 GREY
4. CONSTRUCTION PER UL 1008 STANDARD.
5. FRONT ACCESSIBLE UNIT. NO SIDE OR REAR ACCESS REQUIRED.
6. SUITABLE WIRE BENDING SPACE PROVIDED PER THE SAFETY AGENCY STANDARDS.
7. UL AND CSA RECOGNIZED/CERTIFIED MECHANICAL LUGS ARE STANDARD.
8. EQUIPMENT GROUND LUG IS PROVIDED IN ALL UNITS. REFER TO SHEET 2 FOR DETAILS.
9. ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SHOWN IN INCHES(MILLIMETERS).
10. 100% RATED SOLID/SWITCHED NEUTRAL PROVIDED PER THE SWITCH CONFIGURATION.
11. SUITABLE FOR TOP AND/OR BOTTOM CABLE ENTRY.
12. LARGER SIZE CABINET REQUIRE FOR HEATER AND METER OPTION.
13. FOR WORKING CLEARANCE REFER TO NATIONAL AND LOCAL CODES AND STANDARDS.

SEISMIC NOTES:


1. CENTER OF GRAVITY DIMENSIONS ARE FOR REFERENCE ONLY.
2. BOLT ENCLOSURES USING THE FOLLOWING SEISMIC CERTIFIED MOUNTING HARDWARE PER MOUNTING HOLE: (HARDWARE PROVIDED BY INSTALLER).
 - *3/8-16 GRADE 5 BOLT TORQUE TO 31 FT.-LBS. (42 NEWTON METERS).
 - *3/8 FLAT WASHER
 - *3/8 LOCK WASHER.

	DRAWING FILE 50C-1060	MODEL FILE 50C-1060				
	DATE MODIFIED 12-Apr-21 09:43:50 AM	DESIGNED BY APP				
Calculated for: VOLUME 0.000 in³	CNP C112585 ⬡ Critical to Quality Characteristic	APPROVED BY SR	TITLE ZENITH-ZTX/ZTG, T-SERIES LAYOUT 30A-200A, NEMA 1			
MASS 0.000 lbm	MATERIAL SPECIFICATION ---	FINISH SPECIFICATION ---	UNITS in	LOCAL TITLE ---		
UNLESS OTHERWISE SPECIFIED	MATERIAL DESCRIPTION ---		SIZE D	ROOT NUMBER 50C-1060	REV 3	RELEASE STATE Released
TOLERANCE ON: 1/8 DECIMALS = 0.1 2/16 DECIMALS = 0.02 3/16 DECIMALS = 0.005 ANGLES = 1.0	FINISH DESCRIPTION ---		SCALE 9:100	PRODUCT LINE ZTX/ZTG(D)		SHEET 1 of 2

ABB PROPRIETARY AND CONFIDENTIAL INFORMATION
The information contained in this document has to be kept strictly confidential.
Any unauthorized use, reproduction, distribution or disclosure to third parties is strictly forbidden.
ABB reserves all rights. Copyright © 2024 ABB. All rights reserved.




SECTION D-D
DOOR INSIDE VIEW




SECTION A-A
SCALE 1:5
LEFT SIDE
WITHOUT SIDE PANEL

EQUIPMENT
GROUND LUG
QTY-1
(#8-3/0)


TruONE ATS
(4 POLE SHOWN)



FRONT VIEW
WITHOUT DOOR



SECTION C-C
TOP VIEW
WITHOUT TOP PANEL



SECTION B-B
RIGHT SIDE
WITHOUT SIDE PANEL

ABB			
SIZE D	NUMBER 50C-1060	REV 3	
SCALE 9:100	PRODUCT LINE ZTX/ZTG(D)	SHEET 2 of 2	