



Test Report				Date of issue: 25.5.2015					
Customer:				Serial No.:					
Customer ref.:				Order No.:					
				Type: M3BP 160MLC 2					
				Product Code: 3GBP161430-ADK					
Rating:									
		V	Hz	kW	r/min	A	cos φ	Duty	
3-Motor		690	Y 50	18,5	2942	17,9	0,93	S1	
Insul.cl.F		400	D 50	18,5	2942	30,8	0,93	S1	
IP55		660	Y 50	18,5	2935	18,9	0,93	S1	
		380	D 50	18,5	2935	32,6	0,93	S1	
		415	D 50	18,5	2948	30,0	0,92	S1	
		460	D 60	18,5	3551	26,8	0,93	S1	
Eff class IE3		50Hz : IE3-93,1(100%)-93,9(75%)-93,9(50%) 60Hz : IE3-92,9(100%)							
Resistance				Insulation resistance at 22,1 °C					
Line				R > 2000 Mohm 1000 V					
Ambient: 20,6 °C				Overload					
U ₁ - V ₁				Current 150 % 120s					
U ₁ - W ₁				Torque 160 % 15s					
V ₁ - W ₁				Speed 120 % 120s					
0,2242 Ω									
0,2234 Ω									
0,2238 Ω									
				High-voltage test winding 2400 V 60 s					
Test	Torque [Nm]	Line U[V]	f[Hz]	Input I[A]	P1 [kW]	Output P2 [kW]	η[r/min]	cos φ	η [%]
No load test		399 D	50	8,1	0,41		3000	0,07	
Locked rotor test		60 D	50	32,9	1,34		0	0,39	
Thermal test (100% load)	60,0	400 D	50	31,6	19,91	18,50	2947	0,91	92,90
Partial load points:									
~75% load	44,3	400 D	50	23,9	14,70	13,75	2962	0,89	93,50
~50% load	28,2	400 D	50	16,7	9,44	8,80	2976	0,81	93,27
~25% load	13,9	400 D	50	11,1	4,81	4,34	2989	0,62	90,22
Temperature rise at rated load.				[°C]	[K]	Method	Measurement method		
Stator winding :				49,5	1	1 Resistance			
Frame :				27,8	2	2 Thermometer			
Bearing D-end :				31,4	2	3 Thermocouples			
Ambient Temperature :				22	2				
These tests have been carried out on motor no. 3GV12108464070004, on date 2012-01-18 which is identical in electrical design with the above. Manufactured and tested in accordance with rules of IEC 60034-1 and IEC 60034-2-1. PLL determined from residual loss. On behalf of customer On behalf of manufacturer Date of test Tested by ABB AB, LV Motors, 721 70 Västerås, Sweden Telephone +46 (0)21 32 90 00 Telefax +46 (0)21 32 90 22									

Computer print-out valid without signature.