



Test Report				Date of issue: 4.6.2014					
				Serial No.: 3GF11094418					
Rating:				Order No.: 599608-6					
				Type: M3KP 200MLE 2 IMB3/IM1001					
				Product Code: 3GKP201450-ADG222					
				Protection type: Ex de IIB T4 Gb					
				Cert. No.: LCIE 10 ATEX 3061X / IECEx LCI 04.0011X					
3-Motor		V	Hz	kW	r/min	A	cos φ	Duty	
Insul.cl.F		690	Y 50	45	2944	45,9	0,88	S1	
IP55		400	D 50	45	2944	79,1	0,88	S1	
		415	D 50	45	2949	76,1	0,88	S1	
Eff class IE1		50Hz: IE1 - 92.3(100%) - 92.5(75%) - 91.8(50%)							
Resistance Line				Insulation resistance at 47,0 °C					
Ambient: 20,5 °C				12000 MΩ 1000 V					
U ₁ - V ₁				0,07970 Ω					
U ₁ - W ₁				0,07982 Ω					
V ₁ - W ₁				0,07974 Ω					
				High-voltage test winding 2900 V 1 s					
Test	Torque [Nm]	Line U[V]	f[Hz]	Input I[A]	P1 [kW]	Output P2 [kW]	n[r/min]	cos φ	η [%]
No load test		400,0 D	50	20,7	1,24		2998	0,09	
Locked rotor test		76,0 D	50	79,1	3,87		0	0,37	
Thermal test (100% load)	146,0	400,1 D	50	79,4	48,6	45,0	2945	0,88	92,7
Partial load points:									
~75% load	109,5	400,0 D	50	60,7	36,3	33,8	2958	0,86	93,0
~50% load	72,8	400,0 D	50	43,5	24,3	22,5	2972	0,81	92,5
~25% load	36,4	400,0 D	50	28,8	12,7	11,3	2983	0,63	88,9
Temperature rise at rated load.				°C	K	Method		Measurement method	
Stator winding :				70,7	1	1		1 Resistance	
Frame :				25,8	2	2		2 Thermometer	
Bearing D-end :				47,2	2	3		3 Thermocouples	
Ambient Temperature :				25,0	2				
Vibration:		↓	→						
D-end		0,90	0,90						
N-end		0,60	0,80						
Axial		0,50							
Manufactured and tested in accordance with rules of IEC 60034-1 and IEC 60034-2-1. PLL determined from residual loss.									
On behalf of customer									
On behalf of manufacturer				Date of test 17.12.2011					
Tested by ABB Oy, Motors and Generators, Vaasa, Finland						Telephone +358 10 2211 Telefax +358 10 22 47372			

Computer print-out valid without signature.