


We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden. © ABB '19

On-load tap-changer type (V)UCGL./F, (V)UCLL./F, UCCL./F,  
18 positions, linear switching.  
Min. effective No. of turns in pos. 1.  
The tap-changer is delivered set in pos. 9,  
the preceding pos. was 8.

Lindningskopplare typ (V)UCGL./F, (V)UCLL./F, UCCL./F,  
18 linjär koppling.  
Min antal effektiva varv i läge 1.  
Lindningskopplaren levereras inställd i läge 9,  
föregående läge var 8.



Pos. Läge	Tap selector and diverter switch connect	
1	1-V-x	30
2	2-H-v	
3	3-V-x	
4	4-H-v	
5	5-V-x	
6	6-H-v	
7	7-V-x	
8	8-H-v	
9	9-V-x	
10	10-H-v	
11	11-V-x	
12	12-H-v	
13	13-V-x	
14	14-H-v	
15	15-V-x	
16	16-H-v	
17	17-V-x	
18	18-H-v	

The tap-changer is shown in pos. 9,  
the preceding pos. was 8.  
The tap selector is seen from above.  
Contact arm V is located above contact arm H.

Lindningskopplaren visad i läge 9,  
föregående läge var 8.  
Väljaren sedd uppifrån.  
Kontaktarm V ligger över kontaktarm H.

Continuous lines show leads included in the  
tap-changer. Dashed lines show leads belonging  
to the cleats and leads.

Heldragna linjer visar ledare som ingår i  
lindningskopplaren. Streckade linjer visar  
ledare som tillhör anslutningsdonet.

Sheet	Cont					
	Year	Week				
Form No.	Dept					
	Rev Ind	Revision	Appd	Year	Week	
Design checked by	Accepted by qual control	Accepted for prod by		Description (English)		DATAORIGINAL
	L.Oberg	M.Haggmar		CONNECTION DIAGRAM		
	Design checked by	Drawn by			Description (own language)	
H.Sundberg	A.Wang	KOPPLINGSSHEMA			Lang	Sheet
Drawn by	Drawing checked by	Issued by Dept	Year	Week	1ZSC004308-AAP	
	N.Gustavsson	CO/TK	14	02		
<b>ABB</b>					Rev Ind	Cont
						-