





**OVR BT2 2 20-75 P TS**  
 Order code : 2TAM 1020 00 R 31 01  
 EAN code : 6 940 342 27452 0



OVR BT2 2 20-75 P TS



Overall dimensions (in mm)



Operating diagram

**Pluggable Unit**

**Electrical characteristics**

Types of networks		LV
Number of poles		2
Type / test class		T2 / II
Type of current		A.C./D.C.
Nominal voltage Un	V	57
Maximal continuous operating voltage Uc (L1-PE / L2-PE)	V	150/75
Voltage protection level Up at In (L1-PE / L2-PE)	kV	1.0 / 0.5
Voltage protection level Ures at 3 kA (L1-PE / L2-PE)	kV	0.75 / 0.35
Voltage protection level Ures at 5 kA (L1-PE / L2-PE)	kV	0.8 / 0.4
Nominal discharge current In (8/20)	kA	10
Maximal discharge current Imax (8/20)	kA	20
TOV withstand Ut	V	N/A
Follow current If	A	None
Response time	ns	25
Operating current Ic	mA	< 1
Short circuit withstand Icc	kA	50
Degree of protection		IP 20
Disconnecter		
Curve C Circuit breaker	A	<125
gG - gL fuse	A	<125

**Mechanical characteristics**

Wire range		
Solid wire	mm <sup>2</sup>	2.5...25
Stranded wire	mm <sup>2</sup>	2.5...16
Stripping length	mm	12.5
Tightening torque	Nm	2
Overall dimensions		
Length	mm	64
Width	mm	36
Height	mm	93
Integrated thermal disconnecter		Yes
State indicator		Yes
Safety reserve		No
TS remote indicator		Yes
Contact complement		/
Minimal load		/
Maximal load		/
Connection cross section	mm <sup>2</sup>	/

**Miscellaneous characteristics**

Stocking temperature	°C	- 40 to +80
Operating temperature	°C	- 40 to +80
Maximal altitude	m	2000
Weight	g	200
Color of Housing		PC grey RAL 7035
Fire resistance according to UL 94		V0
Reference standards		GB 18802.1 / IEC 61643-1

**Replacement cartridges**

OVR BT2 20-75 C	2TAM 1010 00 R 31 00
-----------------	----------------------