

TECHNICAL DATA SHEET

Terminals, fork

Un-insulated

Spec-Kon[®]

**Features:**

- Corrosive resistant plating
- Brazed seam crimp

Maximum rating:

- Copper conductors only

Application tool:

- ERG9001

Un-insulated fork terminals for wire termination of copper conductors ranging from 0.5mm² to 6mm²

Certifications / Standards:**Conforms to:**


- IEC 60352-2

Materials / Finishes:

- Copper terminal
- Electro-Tin plated

Terminals, fork:
Un-insulated

Product selection

Drawing	Part no:	Wire size range (mm ²)	Dimensions (mm)					Crimping tool
			d2	L	F	W	D	
	F1.5-3	0.5-1.5	M3	16.0	6.5	5.7	3.4	ERG9001
	F1.5-35	0.5-1.5	M3.5	16.0	6.5	6.4	3.4	
	F1.5-4	0.5-1.5	M4	16.0	6.5	8.1	3.4	
	F1.5-5	0.5-1.5	M5	16.0	6.5	9.5	3.4	
	F1.5-6	0.5-1.5	M6	22.0	11.0	12.0	3.4	
	F2.5-3	1.5-2.5	M3	16.0	6.5	5.7	4.0	
	F2.5-35	1.5-2.5	M3.5	16.0	6.5	6.0	4.0	
	F2.5-4	1.5-2.5	M4	16.0	6.5	8.1	4.0	
	F2.5-5	1.5-2.5	M5	16.0	6.5	9.3	4.0	
	F2.5-6	1.5-2.5	M6	22.0	11.0	12.0	4.0	
	F6-35	4.0-6.0	M3.5	18.5	7.0	8.3	5.5	
	F6-4	4.0-6.0	M4	18.5	7.0	9.0	5.5	
	F6-5	4.0-6.0	M5	18.5	7.0	9.0	5.5	
	F6-6	4.0-6.0	M6	24.5	12.0	12.0	5.5	
	F6-8	4.0-6.0	M8	23.5	11.5	14.0	5.5	

Note: Products must be installed in accordance with applicable national and local electrical codes.