

SAFETY PRODUCTS

MKEY 5 Series Safety Switch Data Sheet

MKey 5 is a mechanical safety switch used for monitoring doors and hatches.

The switch is mounted on the frame and the actuator key on the moving part of the guard.

Option for a stainless steel head is also available.



Easy to install

Variety of actuators

Many types of actuators available depending on application.

Easy mounting

Rotating head allows for up to 8 actuating positions allowing for many mounting possibilities.



Continuous operation

Protect against unwanted stops

“Double wide seal gaskets” enables switches to keep its IP rating for the life of the switch.

Long Mechanical Life

Cam system in switches all rotate the same direction reducing wear giving long mechanical life and good tolerance to misalignment.



Optimum Interface

Small Design

Small footprint makes it easy to install in restricted space.

Industry Footprint

Standard industry footprint for smaller mechanical switches and ½ NPT conduit entry.

Ordering Information

Description	Material Housing	Material Head	Type	Order code
MKEY 5, ½ NPT, No Key	Polyester	Polyester	MKEY 5	2TLA050003R1000
MKEY 5 ½ NPT, Standard Key	Polyester	Polyester	MKEY 5	2TLA050003R1100
MKEY 5, ½ NPT, Flat Key	Polyester	Polyester	MKEY 5	2TLA050003R1200
MKEY 5, ½ NPT, Plastic Flex Key	Polyester	Polyester	MKEY 5	2TLA050003R1300
MKEY 5, ½ NPT, Metal Flex Key	Polyester	Polyester	MKEY 5	2TLA050003R1400
MKEY 5, ½ NPT, SS Flex Key	Polyester	Polyester	MKEY 5	2TLA050003R1500
MKEY 5+, ½ NPT, No Key, 40N	Polyester	Polyester	MKEY 5+	2TLA050003R1001
MKEY 5+ ½ NPT, Standard Key, 40N	Polyester	Polyester	MKEY 5+	2TLA050003R1101
MKEY 5+, ½ NPT, Flat Key, 40N	Polyester	Polyester	MKEY 5+	2TLA050003R1201
MKEY 5+, ½ NPT, Plastic Flex Key, 40N	Polyester	Polyester	MKEY 5+	2TLA050003R1301
MKEY 5+, ½ NPT, Metal Flex Key, 40N	Polyester	Polyester	MKEY 5+	2TLA050003R1401
MKEY 5+, ½ NPT, SS Flex Key, 40N	Polyester	Polyester	MKEY 5+	2TLA050003R1501
MKEY 5, ½ NPT, No Key	Polyester	Stainless Steel	MKEY 5	2TLA050003R1010
MKEY 5 ½ NPT, Standard Key	Polyester	Stainless Steel	MKEY 5	2TLA050003R1110
MKEY 5, ½ NPT, Flat Key	Polyester	Stainless Steel	MKEY 5	2TLA050003R1210
MKEY 5, ½ NPT, Plastic Flex Key	Polyester	Stainless Steel	MKEY 5	2TLA050003R1310
MKEY 5, ½ NPT, Metal Flex Key	Polyester	Stainless Steel	MKEY 5	2TLA050003R1410
MKEY 5, ½ NPT, SS Flex Key	Polyester	Stainless Steel	MKEY 5	2TLA050003R1510
MKEY 5+, ½ NPT, No Key, 40N	Polyester	Stainless Steel	MKEY 5+	2TLA050003R1011
MKEY 5+ ½ NPT, Standard Key, 40N	Polyester	Stainless Steel	MKEY 5+	2TLA050003R1111
MKEY 5+, ½ NPT, Flat Key, 40N	Polyester	Stainless Steel	MKEY 5+	2TLA050003R1211
MKEY 5+, ½ NPT, Plastic Flex Key, 40N	Polyester	Stainless Steel	MKEY 5+	2TLA050003R1311
MKEY 5+, ½ NPT, Metal Flex Key, 40N	Polyester	Stainless Steel	MKEY 5+	2TLA050003R1411
MKEY 5+, ½ NPT, SS Flex Key, 40N	Polyester	Stainless Steel	MKEY 5+	2TLA050003R1511

NOTE: Anything in **bold** is typically stocked.**Accessories**

Description	Material Housing	Order code
Standard Key	Stainless Steel	2TLA050040R0202
Flex Key with metal housing	Stainless Steel	2TLA050040R0203
Flex Key with stainless steel housing	Stainless Steel	2TLA050040R0204
Flat Key	Stainless Steel	2TLA050040R0220
½ NPT Cable Gland	Stainless Steel	2TLA050040R0001

NOTE: Anything in **bold** is typically stocked.

Technical Data	
Manufacturer	
Address	ABB Electrification Sweden AB / JOKAB SAFETY Varlabergsvägen 11 SE-434 39 Kungsbacka Sweden
Electrical characteristics	
Utilization category	AC-15 A300 3A
Thermal current	10A
Rated insulation/withstand voltages	500 VAC/2500 VAC
Contacts	2NC + 1NO
General	
Travel for positive opening	6 mm
Actuator entry minimum radius	175 mm Standard Key 100 mm Flexible Key
Protection class	IP67
Ambient temperature	-25...+80°C
Size	See manual
Conduit entries	½ NPT
Material	Polyester (Head Polyester or S/Steel 316)
Fixing	Body: 2 x M5 Actuator: 2 x M5
Maximum approach / withdrawal speed	600 mm/s
Holding Force	MKEY 5: 12N MKEY 5+: 40N
Vibration	IEC 68-2-6, 10-55 Hz+1 Hz, Excursion: 0.35 mm, 1 octave/min
Safety-related characteristic data and Conformity	
Conformity	European Machinery Directive 2006/42/EC EN ISO 12100:2010, EN 1088:1995+A2:2008, EN 60204-1:2006+A1:2009 EN 60947-1:2007+A1:2011, EN 60947-5-1:2004+A1:2009
EN ISO 13849-1	Up to PL e, Cat. 4 depending on system architecture
EN 62061	Up to SIL3 depending on system architecture
Safety data	
B10d	2,500,000 operations at 100 mA load
MTTFd	356 years (8 cycles per hour / 24 hours per day / 365 days per year)
Certifications	TÜV, cULus
Information with regard to UL 508	Use 12AWG copper conductors only Electrical Rating: A300 48W5 Type 1 Enclosure Max. Switching Current / Volt / Amp: 120V 6A (720VA break) PF 0.38, 240V 3A (720VA break) PF 0.38.

NOTE: A single MKey5 can achieve performance level PL c according to EN ISO 13849 if used correctly with an ABB Jokab Safety safety relay, Pluto safety-PLC or Vital safety module. If two MKey5-switches are used for the same safety function, a performance level up to PL e can be achieved. Refer to EN ISO 13849 for details on how to achieve this if necessary.

—
ABB Inc.
305 Gregson Drive
Cary, North Carolina 27511
United States
electrification.us.abb.com/
products/machine-motor-control

—
We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB AG does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

—
We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB AG.
Copyright© 2022 ABB
All rights reserved