


# Serenga 2

Project covering & stylish



### Surface mount downlight in black

- Injection moulded - high grade polycarbonate body
- Specially designed lens for optimised light distribution
- Modular, First-Fix installation
- Ease of installation - unique moulded construction to retain IP rating without additional protection
- Escape route supplied as standard




Luminaire

Order code	Description	Input voltage	Lamp type	Lamp output (lm)	Power consumption (VA/W)	Operation / duration (hrs)	Environment temp. (°C)	Weight (kg)
CTSR2-SEM3-A1B	SFC M3 CT-NAVEO ESC-L4M BLK	220-240 AC 50Hz			3.5 / 3	3	5-40	1.0
SR2-SEM3-A1B	SFC M3 AUTOTST ESC-L4M BLK	220-240 AC 50Hz			3.5 / 3	3	5-40	1.0
SR2-SE230LT-A2	SFC 230V EMEX ESC-L4M BLK	220-240 AC 50/60Hz			3.5 / 3	230V	0-40	0.7
SR2-SE230-A2	SFC 230V SL 230V50HZ BLK ESC-L4M 2L	220-240 AC/DC 0-60Hz			3.5 / 3	230V	0-40	0.7

### Select optical lens for application required

Code	Lens	Type	Application
SR2-LENS1*	A	Escape route	2-4m corridor use, ceiling mount
SR2-LENS2	B	Escape route, or object	4-8m corridor use, ceiling mount. Or spot light at 2-4m (ceiling mount)
SR2-LENS3	C	Escape route	8-12m corridor use, ceiling mount
SR2-LENS4	D	Open area	2-4m, open area space
SR2-LENS5	E	Open area	4-8m, open area space
SR2-LENS6	F	Open area	8-12m, open area space
SR2-LENS7	G	Escape route	2-4m corridor use, wall mount

\*Lens included in the box  
See spacing tables on pages 128-129



IP Rating	Product type
IP42	wall mount
IP54	ceiling mount

