

SACE® Tmax® XT Molded Case Circuit Breakers

XT2 – 125A Frame Size



125 A frame available up to 600 V UL. Thermal-magnetic, MCS, MCP basic and advanced trip units. Max interrupt rating of 200 kA at 480 V, 42 kA at 600 V. Electronic trip units, high interrupt ratings, communications and embedded logic.

Molded Case Circuit Breaker (MCCB)		XT2						
Frame Size		[A]	125					
Poles		[No.]	3, 4					
Rated Voltage	(AC) 50-60 Hz	[V]	600					
	(DC)	[V]	500					
Versions			Fixed, Plug-in, Withdrawable					
Interrupting Ratings			N	S	H	L	V	X
240 VAC	[kA]	65	100	150	200	200	200	
480 VAC	[kA]	25	35	65	100	150	200	
600Y/347 VAC	[kA]	-	-	-	-	-	-	
600 VAC	[kA]	18	22	25	35	42	42	
250 VDC 2p in series	[kA]	35	50	65	75	85	85	
500 VDC 2p in series	[kA]	-	-	-	-	-	-	
500 VDC 3p in series	[kA]	35	50	65	75	85	85	
500 VDC 4p in series	[kA]	-	-	-	-	-	-	
600 VDC 3p in series	[kA]	-	-	-	-	-	-	
Mechanical Life		[No. Operations]	25,000					
		[No. Hourly Operations]	240					
Dimensions - Fixed (W x D x H)	3p	[mm]/[in.]	[90 x 82.5 x 130]/[3.54 x 3.25 x 5.12]					
	4p	[mm]/[in.]	[120 x 82.5 x 130]/[4.72 x 3.25 x 5.12]					
Weight	Fixed 3p/4p	[kg - lb]	[1.2 - 2.65]/[1.6 - 3.53]					
	Plug-in (EF) 3p/4p	[kg - lb]	[2.54 - 5.6]/[3.27 - 7.21]					
	Withdrawable (EF) 3p/4p	[kg - lb]	[3.32 - 7.32]/[4.04 - 8.91]					

Compliance with standards

SACE® Tmax XT circuit breakers and their accessories are constructed in compliance with¹:

- Standards
 - UL489 (MCCB File # E93565, MCS File # E116595, & Accessories File # E116596) and CSA C22.2;
 - HACR Type
- Directives
 - EC “Low Voltage Directive” (LVD) N° 2014/35/EC;
 - EC “Electromagnetic Compatibility Directive” (EMC) 2014/30/EC;
- Shipping Registers approvals upon request.

Terminal options

Fixed version:

The standard fixed version of the SACE® Tmax XT circuit breakers are supplied with front terminals (F) and can be fitted with the following types of terminals as accessories using special kits:

- Extended front (EF)
- Extended spread front (ES)
- Front for copper/aluminum cables (FCCuAl)
- Front for copper cables (FCCu)
- For flexible busbars (FB)
- Multicable (MC)
- Rear oriented (R)

Plug-in and Withdrawable versions:

Please see the [Tmax XT Technical Catalog](#) for more details.

Trip unit options

- Thermal Magnetic Fixed (TMF)
- Thermal Magnetic Adjustable (TMA)
- Ekip Dip (LS/I, LSI, LIG, LSIG)
- Ekip Touch (LSI, LSIG)
- Ekip Touch Measuring (LSI, LSIG)
- Ekip Hi-Touch (LSI, LSIG)
- Ekip M Dip (I)
- Ekip M Touch (LRIU)
- Motor Circuit Protector (MCP)
- Molded Case Switch (MCS)

Accessories

- Terminal Options
- Auxiliary Contacts
- Operating Mechanisms (Direct Handles, Extended Handles, Flange Handles, etc.)
- Remote Control (Shunt Trip, Undervoltage Release, Motor Operator, etc.)
- Safety and Protection (Terminal Covers, Phase Separators, Padlocks, Keylocks, IP Protection, etc.)
- Interlocks
- Residual Current Devices

Included with the breaker

The breaker comes with breaker mounting hardware, terminal hardware, phase barriers, and an insulation backplate.

Temperature rating

Tmax XT circuit breakers can be used in ambient air temperatures varying between -25°C and +70°C, and can be stored at temperatures between -40°C and +70°C. Please consult the [temperature performance derating tables](#) for temperature values outside of +40°C. The reference temperature for the trip units is +40°C. Note that the lug and wire insulation ratings are +75°C, so care should be exercised when operating near this temperature in order not to exceed these ratings.

100% rated

A Fixed XT2 breaker is suitable for continuous operation at 100-percent of rating up to 100A with thermal magnetic trip unit and up to 125A with electronic trip unit.

Current limiting

XT2H, XT2L, and XT2V breakers have undergone tests per the UL489 Standard and are classified as UL current limiting circuit breakers. They have specific characteristics in terms of limiting peak current and specific let-through energy. This pertains to only TMF and TMA with $I_n = 15-125A$ and Ekip trip units with $I_n = 10, 25, 60, 100, 125A$.

Single phase application

XT2 three pole circuit breakers, equipped with thermal-magnetic trip units, can be used in single phase applications. For this purpose, they are marked as follows according to UL standard: Suitable for single phase application up to 347VAC.

Reverse feed capabilities

Power can be supplied from bottom terminals of the XT2 breaker up to a maximum of 480V.

Related links

[Installation Instructions](#)

Drawings

- [XT2 Fixed 3-4p breaker \(2D\)](#)
- [XT2 Fixed 3p breaker \(3D\)](#)
- [XT2 Fixed 4p breaker \(3D\)](#)

1. Product complies with listed standards and directives as of the date of this publication