

HVC200 | HVC300 | HVC360

# Distributed Power for Heavy-Duty Fleets



Reliable  
Performance

**360 kW**

Distributed Power

Simultaneous  
Charging

**≤ 4**

Dispensers in Parallel

Flexible Site  
Setup

**≤ 150 m**

Between Cabinet and  
Dispenser

# Power Specification

<b>DC Output:</b>	<p>Output power shared between 1 - 4 outlets: Configurable as 200 kW, 300 kW, or 360 kW Dynamic Power Sharing (granularity): <b>HVC200:</b> 50 kW   <b>HVC300:</b> 75 kW   <b>HVC360:</b> 90 kW Output current (peak): <b>HVC200:</b> 285 A at 700 V DC, 250 A at 800 V DC <b>HVC300:</b> 430 A at 700 V DC, 375 A at 800 V DC <b>HVC360:</b> 500 A at 720 V DC, 450 A at 800 V DC Output voltage: 150 - 940 V Configuration of outlets: can be connected to 1 - 4 dispensers Power conversion efficiency: up to 96% Standby power: 130 W</p>
-------------------	---

<b>AC Input:</b>	<p>Nominal voltage: (CE): 400 Vac (<math>\pm 10\%</math>) (NA): 480 Vac (<math>\pm 10\%</math>) Nominal input current (RMS): <b>HVC200:</b> (CE): 315 A (NA): 262 A <b>HVC300:</b> (CE): 470 A (NA): 392 A <b>HVC360:</b> (CE): 560 A (NA): 470 A AC power rating: <b>HVC200:</b> (CE): 218 kVA (NA): 218 kVA <b>HVC300:</b> (CE): 326 kVA (NA): 326 kVA <b>HVC360:</b> (CE): 390 kVA (NA): 391 kVA Frequency: (CE): 50 Hz (<math>\pm 4\%</math>) (NA): 60 Hz (<math>\pm 4\%</math>) Earthing systems: TN-C, TN-C-S, TN-S, TT Inlet cable size: 3P + PE up to: 240 mm<sup>2</sup>/500 MCM AWG Power factor: <math>\geq 0.98</math> (Output power <math>\geq 10</math> kW) Total Harmonic Distortion (THD): <math>&lt; 5\%</math> Overvoltage category: III SPD: Type 2 SCCR: (CE): 25 kA (NA): 65 kA</p>
------------------	--

# System Specification

<b>Operating Conditions:</b>	<p>Operating from -30°C to 55°C (-22°F to 131°F) with derating Storage from 5°C to 40°C (41°F to 104°F), IEC 60721-3-2</p> <p>Altitude: up to 2000 m (6562 ft) Humidity: up to 95%, non-condensing Impact resistance: IK10 IP rating: IP54</p> <p>Noise emission: 61 dB(A) at 1 m front side, 20°C (68°F), full power</p> <p>Intended use: indoor and outdoor Mounting options: floor mounted Environment pollution degree: Class 3 (outside), Class 2 (inside)</p>
<b>Form Factor:</b>	<p>Dimensions (H x W x D): 2180 x 1170 x 770 mm (85.8 x 46.1 x 30.3 in) Weight: <b>HVC200:</b> 830 kg (1830 lbs) <b>HVC300:</b> 890 kg (1962 lbs) <b>HVC360:</b> 950 kg (2094 lbs) Enclosure type: AISI 430 stainless steel Corrosion resistance: C5-H, ISO 12944</p>

# Customer Interface

<b>Charging Interface Options:</b>	Connector based (CCS1/2), Panto Down and Panto Up
<b>Lighting:</b>	4 RGB LEDs, 1 per outlet
<b>Emergency Button:</b>	External EMG button (optional)
<b>Service Access:</b>	Front door
<b>Remote Management:</b>	Access control, configuration, diagnostics, software updates <sup>1</sup>

## Connection Cabinet - Dispenser

<b>Compatible Dispensers:</b>	ChargeDock, HVC Control Box, HVC Depot Charge Box
<b>DC Power Cable:</b>	(CE): 2 or 4 x 185 mm <sup>2</sup> (max.) (NA): 2 or 4 x 350 MCM AWG (max.)
<b>Auxiliary AC Supply from Cabinet:</b>	(CE): 230 V AC (3 x 4 mm <sup>2</sup> ) (NA): 110 V AC (3 x 12 AWG)
<b>Interlock Cables:</b>	(CE): 2 x 2 x 0.75 mm <sup>2</sup> + shield (NA): 2 x 2 x AWG18 + shield
<b>Distance &amp; Communication:</b>	(CE): Ethernet (up to 100 m), optional: Fiber (up to 150 m) (NA): Fiber (up to 150 m / 492 ft)

## Standards & Compliance

<b>Safety Standards:</b>	IEC 61851-1 ed 3, IEC 61851-23 ed 1, IEC 61851-24 ed 1, IEC 62196-2, IEC 62196-3, UL 2202, CSA 22.2
<b>Metering:</b>	(CE): Eichrecht (for select dispensers)
<b>EMC:</b>	61851-21-2
<b>Electrical Safety:</b>	(CE): IEC 61439-7 (NA): NEC (NFPA 70)
<b>Manufactured:</b>	USA & Europe
<b>Network Connections:</b>	3G/4G, Ethernet (RJ45)
<b>OCPP:</b>	OCPP 1.6 JSON, OCPP 2.0.1 (in development)
<b>Vehicle Communication Protocol:</b>	DIN 70121, ISO/IEC 15118 series ed 1 with EIM, Autocharge, OppCharge, J3105-1 ed 1 and ed 2
<b>Additional Standards:</b>	Cabinet IP rating according to IEC 60529: 1989+AMD2: 2013+COR1: 2019
<b>Expected Lifespan:</b>	10 years <sup>2</sup>

<sup>1</sup> Subject to Service Package coverage

<sup>2</sup> Subject to Service Package coverage, potential refurbishment, and environmental operating conditions including proximity to sea water, conductive dust, and condensing humidity. Under certain conditions and for certain models this can be extended to 15 years.

—  
©Copyright ABB E-mobility 2026. All rights reserved to copyrights, registered trademarks, and trademarks reside with their respective owners. The information in this document is provided in good faith, is provided for information purposes only and is subject to contract. The information contained herein is subject to change without notice and should not be construed as any commitment by ABB E-mobility B.V. or its affiliates or holding companies (ABB E-mobility). ABB E-mobility assumes no responsibility for any errors that may appear in this document. We reserve all rights with respect to this document, its content and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB E-mobility. No representations are made, express or implied, with respect to the accuracy, reliability, availability or completeness of the information provided, and no liability is accepted for any damage or loss suffered as a result of reliance on any information provided herein.

—  
**ABB E-mobility B.V.**

Heertjeslaan 6  
2629 JG Delft  
The Netherlands  
Phone: +31 88 4404600  
E-mail: [info.evci@nl.abb.com](mailto:info.evci@nl.abb.com)  
**e-mobility.abb.com**

—  
**ABB E-mobility Inc.**

4601 Park Rd, Suite 600  
Charlotte, NC 28209  
United States  
Phone: 1-706-344-2889  
E-mail: [US-evci@abb.com](mailto:US-evci@abb.com)  
**e-mobility.abb.com**

—  
**ABB E-mobility Inc.**

800 Hymus Boulevard  
Saint-Laurent, QC H4S 0B5  
Canada  
Phone: 1-800-435-7365  
E-mail: [CA-evci@abb.com](mailto:CA-evci@abb.com)  
**e-mobility.abb.com**