

Stanilite®

Platinum exit LED Quickfit® vandal resistant Nexus®



Range

Platinum range

Product group


Exit LED



Features

- LED technology 100,000 hours plus lamp life
- Low power consumption and LED light source for reduced operation and maintenance costs
- IK09 mechanical impact resistance
- Vermin resistance
- Advanced charging technology combined with Lithium iron phosphate battery for long life and low maintenance
- Nexus monitored, either cabled or wireless
- Unique internal steel slide connect bracket for quick installation and easy maintenance
- Strong steel body and end cap
- Anti-tamper cover screws
- Universal wall/ceiling mounting
- Includes all pictograph diffuser options for single or double sided installation

Catalogue no.	Description
Nexus products	
VPQNXSLEDP	Platinum exit LED Quickfit vandal resistant Nexus LX pictograph
VPQNRFLEDP	Platinum exit LED Quickfit vandal resistant Nexus RF pictograph
Spare parts	
03-01302P	Battery LiFePO4 3.2V 3.2Ah
PQFNXSLEDP-FR	Platinum exit LED Quickfit frame only Nexus LX
PQFNRFLEDP-FR	Platinum exit LED Quickfit frame only Nexus RF



Dimensions		
Length	Width	Height
410mm	140mm	265mm
Weight		
Model	Weight	
Nexus LX/RF	7.8kg	
Construction		
Part	Construction	
Body and end cap	Steel body and end cap with anti-tamper cover screws White powder coated finish	
Diffuser	Extra tough UV stabilised polycarbonate	

Light source			
	Model	Light source	
	Nexus LX/RF	Multiple LED 1.6W	

Power consumption			
	Model	Power consumption	
	Nexus LX/RF	3.2W	

Note: Preliminary results

Photometrics			
	Model	Class	Classification
	Nexus LX/RF	C0	E1.25
		C90	E1.25

Note: Preliminary results

Note:

- Designed to comply with AS2293 and meet relevant Australian EMC standards