



## Molded Case Circuit Breaker

### Current Ratings

100, 110 and 125 Amperes

### Voltage Ratings (Max.)

1-pole – 277 Vac (125 Vdc)

2- and 3- pole – 480 Vac (250 Vdc)

### Frequency Ratings

60 Hertz

Type TEYD, TEYH, TEYL 100-125 Amperes

Type TEYF 110-125 Amperes

Enclosure Compensated

Long-time Delay and Instantaneous Time-current Curves

Curves show enclosure-compensated circuit breaker in open air, 40°C ambient, wired with conductors of corresponding rating, no prior load. For all other ambients, use rating shift index at top of sheet.

## DES082

### Adjustments

Long-time delay thermal trip: not adjustable.

Instantaneous magnetic trip: not adjustable.