

**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME**

**CB TEST CERTIFICATE**

Product

Auxiliary Devices

Name and address of the applicant

ABB AB JOKAB SAFETY  
Varlabergsvagen 11  
Kungsbacka, SE-434 39 Sweden

Name and address of the manufacturer

ABB AB JOKAB SAFETY  
Varlabergsvagen 11  
Kungsbacka, SE-434 39 Sweden

Name and address of the factory

ABB Stotz-Kontakt GmbH  
Hauptstrasse 14-16  
Hornberg, 78132 Germany

Note: When more than one factory, please report on page 2

Additional Information on page 2

Ratings and principal characteristics

See Page 2

Trademark / Brand (if any)



Type of Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

BSR10, BSR11, BSR23, SSR10, SSR10M, SSR20, SSR20M, SSR32, SSR42, TSR10, TSR20, TSR20M, USR10, USR22

Additional information (if necessary may also be reported on page 2)

Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60947-1:2007/AMD1:2010, IEC 60947-1:2007/AMD2:2014, IEC 60947-1:2007, IEC 60947-5-1:2016

As shown in the Test Report Ref. No. which forms part of this Certificate

4789281466 issued on 2020-05-04

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2020-05-12

Signature:

Jan-Erik Storgaard



Ref. Certif. No.

**DK-96999-UL**

**Ratings:**

Model BSR11:

AC-15, AC-12: 250Vac, NO. Contact: 5Aac;  
DC-13, DC-12: 24Vdc, NO. Contact: 6Adc.

Models BSR23, BSR10, SSR10, SSR10M, SSR20, SSR20M,  
TSR10, TSR20, TSR20M, and USR10:

AC-15, AC-12: 250Vac, NO. Contact: 5Aac;  
DC-13, DC-12:24Vdc, NO. Contact: 6Adc;  
AC-15, AC-12: 250Vac, NC. Contact: 0.5Aac;  
DC-13, DC-12: 24Vdc, NC. Contact: 2Adc.

Models: SSR32, SSR42 and USR22:

AC-15, AC-12: 250Vac, NO. Contact: 3Aac;  
DC-13, DC-12:24Vdc, NO. Contact: 3Adc.

Operating Voltage - Coil: SSR10, SSR20, TSR10, TSR20, USR10, SSR32, SSR42, USR22, BSR23; 24Vdc.  
SSR10M, SSR20M, TSR20M: 85 Vac – 265 Vac (50/60 Hz) or 120 – 375 Vdc.

**Additional information (if necessary)**



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/names](http://www.ul.com/names)

Date: 2020-05-12

Signature:

Jan-Erik Storgaard