


We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden.  
© ABB '19

On-load tap-changer type (V)UCGL./F, (V)UCLL./F, UCCL./F,  
12 positions, linear switching.  
Min. effective No. of turns in pos. 1.  
The tap-changer is delivered set in pos. 7,  
the preceding pos. was 6.

Lindningskopplare typ (V)UCGL./F, (V)UCLL./F, UCCL./F,  
12 lägen, linjär koppling.  
Min antal effektiva varv i läge 1.  
Lindningskopplaren levereras inställd i läge 7,  
föregående läge var 6.



Pos. Läge	Tap selector and diverter switch connect	
1	1-V-x	30
2	2-H-v	
3	3-V-x	
4	4-H-v	
5	5-V-x	
6	6-H-v	
7	7-V-x	
8	8-H-v	
9	9-V-x	
10	10-H-v	
11	11-V-x	
12	12-H-v	

The tap-changer is shown in pos. 7,  
the preceding pos. was 6.  
The tap selector is seen from above.  
Contact arm V is located above contact arm H.

Lindningskopplaren visad i läge 7,  
föregående läge var 6.  
Väljaren sedd uppifrån.  
Kontaktarm V ligger över kontaktarm H.

Continuous lines show leads included in the  
tap-changer. Dashed lines show leads belonging  
to the cleats and leads.

Heldragna linjer visar ledare som ingår i  
lindningskopplaren. Streckade linjer visar  
ledare som tillhör anslutningsdonet.

Sheet	Cont									
	Year	Week								
Form No.	Dept									
	Rev Ind	Revision	Appd	Year	Week					
Design checked by	Accepted by qual control L.Oberg		Accepted for prod by M.Haggmar		Description (English) CONNECTION DIAGRAM				DATAORIGINAL	
	Design checked by H.Sundberg		Drawn by A.Wang		Description (own language) KOPPLINGSSHEMA				File name	
	Drawing checked by N.Gustavsson		Issued by Dept CO/TK		Year 14	Week 02	1ZSC004308-AAH			
						Lang				
								1	-	