
# **PROFIBUS** with FBP

Achieve everything with fewer components





# FieldBusPlug: the concept

ABB's communications product family comprises a range of switching and automation components that can be easily combined with all common standard fieldbus systems.

#### One device for all fieldbuses


Each complete unit and each function module within the product family has a fieldbus-neutral interface. A specially pre-assembled connection cable acts as a communicative link to its bus-specific plug interface. Process flexibility, transparency and reliability are thereby easily attained. The connection, operating and diagnosis elements are fitted on the front of all units in the series, making for very convenient handling.

#### The components

Fieldbus connection (M 12)

The FieldBusPlug lies at the heart of the product family's communications. These plugs link devices and combinations of devices with different functions and characteristics as well as connecting standard sensors to automation units. The product family also includes a wide range of switching and automation modules, available in power levels suited to real-life applications, e.g. devices for engine protection and control as well as standard sensors.





Connection using the FieldBusPlug

## The applications

As well as supporting numerous important fieldbus types, such as DeviceNet, AS-Interface and Modbus RTU, ABB's FieldBusPlug system also supports PROFIBUS DP, which is currently recognised and promoted around the world as the market leader amongst fieldbus systems. New FBP components offering even more scope for planning and implementation of central and decentralised applications have been developed especially for PROFIBUS DP. Material and processing costs are falling substantially as a result of consistent tuning to PROFIBUS DP circumstances.

PROFIBUS DP plug PDQ22-FBP


# PDQ22-FBP: One bus node for four units


As well as supporting the tried and tested PROFIBUS DP plug PDP22-FBP, ABB's new PDQ22-FBP allows up to four FBP units to be connected to the PROFIBUS DP. This makes the PDQ22-FBP a cost-effective solution, especially when using devices positioned close to one another.

Standard connection cables are used to link the PDQ22-FBP and attached devices.


All devices connected to a node can be configured and maintained separately. Status LEDs provide information about the bus status and devices attached. The failure or removal of one device does not affect communication with the remaining devices.

The PDQ22-FBP makes possible efficient engineering and simple connection to control systems and ensures the level of safety needed for ongoing operations.





Class 2 master (e.g. temporarily connected maintenance tool)






Controller (Class 1 master and optionally C2 master)

# Comprehensive diagnosis offers enhanced transparency





Just like all other FBP components, PDQ22-FBP and PDP22-FBP support a wide range of convenient diagnosis functions. PDQ22-FBP provides detailed diagnosis information about the status of attached units, its own status and that of the PROFIBUS connection. The diagnosis information is displayed both by the local diagnosis LEDs and by the standard PROFIBUS services.

The following errors are recognised:

- Incorrect device address settings
- Device connected to incorrect port
- Incorrect device type
- Missing unit
- No PROFIBUS-communication
- Parameter error

The diagnosis information therefore makes it easier for the user to quickly detect and rectify damage. Time-consuming trouble-shooting is no longer needed and downtimes/maintenance times are kept to a minimum.






# **Effortless process connections**

PDQ22-FBP and PDP22-FBP are certified PROFIBUS participants, which means that they enable simple and proven device integration in any control systems or control units. Both GSD- and DTM-based systems are supported and both PROFIBUS protocols, DP-V0 and DP-V1, are implemented.

All parameter, service and diagnosis data on the attached units can be accessed in a transparent manner, allowing the FBP devices to be integrated in cross-system maintenance management systems.





....

# Use in motor control centres

The FieldBusPlug system is a real winner in terms of installation cost, e.g. if the intelligent UMC22-FBP motor controller is used for drawer or fixed panel systems. The PDQ22-FBP is an optimum solution in this respect too, as it has been designed with separate bus node and devices in mind. The PROFIBUS node can remain in the cable room, while the UMC22-FBP for example is installed in the drawer.


A simple serial connection cable ensures stable communication between the PDQ22-FBP and the UMC22-FBP. Replacing a drawer does not impact on the function of any remaining drawers. Preassembled accessories are available for rapid assembly.





Example of a drawer system

# **Quick start-up**



By using FBP components, you can save both time and money. Not only do these components offer simple engineering and rapid configuration but assembly costs also fall considerably. The new installation concept of the FBP system opens up a whole host of options for applications in central and decentralised applications. Simple incorporation in the process is just one of the system's smart features.






Flexible assembly options.

At top: Screw fastening

Below: With assembly plate on DIN bar

# **Technical data overview**

#### PDP22-FBP



#### **Technical Data PDP22-FBP**

Р	ov	ver	su	p	рl	١

Supply voltage mode via FieldBusPlug cable

24 V DC Supply voltage 19,2 ... 31,2 V DC Voltage range

46 mA Current consumption at 19,2 V at 24,0 V 37 mA

at 31,2 V 31 mA

min. 10 ms power line failure Bridging time

bridging time, to be performed by the power supply unit

Power dissipation max. 0,9 W

Load capacity of cable max. 4 A

Communication

Protocol PROFIBUS DP complying with EN50170

PDP21-FBP DP-V0 PDP22-FBP DP-V0/V1

Certification yes, Z01095

Baudrate max. 12 Mbit/s

Electrical Isolation yes, to the terminal device Address range 1 to 126, recommended 3 to 125

Address setting depending from the terminal device: - address switches on the terminal

device

- addressing set CAS21-FBP

- operating panel

Bus termination active bus termination 150  $\Omega$  acc.

PROFIBUS standard required PDR11-FBP required if PDP22-FBP is

last device on the bus

Construction of the FieldBusPlug cable round cable, magenta

supply voltage 2 x 0,34 mm<sup>2</sup> data 2 x 0,25 mm<sup>2</sup>

LEDs on the front LED1 green status PROFIBUS

LED2 red status PROFIBUS LED3 green status terminal unit LED4 red status terminal unit

Environmental and mechanical data

Mounting on terminal device, fixed with a screw

(provided on delivery)

Dimensions see following


Weight plug with cable 0.25 m 0.09 kg

plug with cable 0.50 m 0.10 kg plug with cable 1.00 m 0.13 kg plug with cable 2.00 m 0.19 kg plug with cable 5.00 m 0.35 kg

-20 ... +70 °C Temperature range storage operation 0 ... +55 °C

Degree of protection IP67

#### PDQ22-FBP



#### **Technical Data PDQ22-FBP**

Power supply	۱

Supply voltage mode via FieldBusPlug cable

Supply voltage 24 V DC

Voltage range 19,2 ... 31,2 V DC

Current consumption at 19,2 V 39 mA at 24,0 V 31 mA

at 31,2 V 24 mA

Bridging time min. 10 ms power line failure

bridging time to be performed by the powersupply unit

Power dissipation max. 0,75 W

Load capacity of PROFIBUS cable max. 4 A

Communication

Protocol PROFIBUS DP-VO/V1 complying

with EN50170

Certification yes

Baudrate max. 12 Mbit/s

Electrical isolation yes, to the connected terminal

devices

Address range 1 to 99
Address setting rotary switches

Address setting rotary switches

Bus termination active bus termination 150  $\Omega$  acc.

PROFIBUS standard required PDR11-FBP required if PDQ22-FBP

is last device on the bus

Cable to the FieldBusPlug system round cable, magenta supply voltage 2 x 0,34 mm²

data 2 x 0,25 mm<sup>2</sup>

Type PDX11-FBP

Cable to the terminal devices standard sensor cable, 5-poles,

shielded

Length max. 2 m

LEDs on the front

terminal device LED DD1 red fault of terminal device

PROFIBUS LED DD2 green terminal device ok LED 3 green communication ok LED 4 red communication error

Environmental and mechanical data

Mounting with screws or with adaptoon DIN-rail

(accessories)

Dimensions see following
Weight 0,2 kg

Temperature range storage -20 ... +70 °C

Operation 0 ... +55 °C

Degree of protection IP67


Ordering data

PDQ22-FBP.0 1SAJ 240 200 R0050

Adaptor for DIN-rail mounting

CDA11-FBP.0 1SAJ 923 300 R0001

# **PROFIBUS** with FBP



Achieve everything with fewer components



#### ABB STOTZ-KONTAKT GmbH

P. O. Box 10 16 80 D-69006 Heidelberg Telephone: ++49 62 21 / 701-0 ++49 62 21 / 701-729 http://www.abb.de/stotz-kontakt

### **ABB Global Contact Directory**

The ABB Contact Directory (http://www.abb.com/contacts/) helps you find local contacts for ABB products in your country. Please select the relevant product group from the dropdown menu to the right or from the page.