



中国国家强制性产品认证证书

证书编号：2024010302658039

认证委托人名称及地址

ABB Oy

Muottitie 2A FI-65320 VAASA, Finland

生产者名称及地址

ABB Oy

Muottitie 2A FI-65320 VAASA, Finland

生产企业名称及地址

ABB Oy

Muottitie 2A FI-65320 VAASA, Finland

产品名称和系列、型号、规格

隔离器熔断器组

OESL630V32D, OEVA630D32D; 详见附页

产品标准和技术要求

GB/T 14048.3-2017

上述产品符合《强制性产品认证实施规则 低压电器 低压元器件》
(CNCA-C03-02:2024) 的要求，特发此证。

发证日期：2024 年 07 月 15 日 有效期至：2029 年 07 月 14 日

证书信息和有效性可扫描下方二维码或登录发证机构网站查验，
也可在认监委网站 (www.cnca.gov.cn) 查询。



签发：

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE


中国质量认证中心有限公司





证书附页：第 1 页 共 3 页

直流接线图如下:



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE



中国质量认证中心有限公司



中国国家强制性产品认证证书

证书编号: 2024010302658039

证书附页: 第 2 页 共 3 页



型号解释:

本页为证书附页, 应与证书主页同时使用。



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司



证书附页：第 3 页 共 3 页

OESL	630	V	32	D	24	V2	
							Rated voltage for trip coil 脱扣线圈额定电压 V1=110VAC V2=230VAC
							Number of poles 极数 02 - 2poles 2极 04 - 4poles 4极 24 - parallell connection by 2poles and 4poles fuse switches 2极和4极隔离开关熔断器组并联
							Fuse holder DIN43620 熔断器座 DIN43620
							Size of intermediate switch 中间开关规格
							Code V for OESL and D for OEVA 代号 V 用在 OESL and D 用在 OEVA
							Size of main switch 主开关规格
							Series Designation 系列号 OESL,OEVA

本页为证书附页，应与证书主页同时使用。



中国质量认证中心有限公司



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO.: 2024010302658039

NAME AND ADDRESS OF THE APPLICANT

ABB Oy
Muottitie 2A FI-65320 VAASA, Finland

NAME AND ADDRESS OF THE MANUFACTURER

ABB Oy
Muottitie 2A FI-65320 VAASA, Finland

NAME AND LOCATION OF THE FACTORY

ABB Oy
Muottitie 2A FI-65320 VAASA, Finland

PRODUCT NAME,MODEL AND SPECIFICATION

Disconnecter-Fuse
OESL630V32D, OEVA630D32D;See the appendix

STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 14048.3-2017

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C03-02:2024).

Valid from: Jul.15,2024

Valid until: Jul.14,2029

The certificate information and validity could be checked by scanning the QR code below or logging in to the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).



SIGNATURE:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO. : 2024010302658039

Appendix: Page 1 of 2

OESL630V32D, OEVA630D32D

U_{imp}: 12kV;

U_i: 1000V;

I_{th}: 600A;

U_e: DC690V, DC1000V;


I_e: 600A;

I_q: 65kA(DC1000V), 100kA(DC690V);

Utilization Category: DC-20B;

IP20(Front only)

The DC connection diagram is as follows:



This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO. : 2024010302658039

Appendix: Page 2 of 2

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation



This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.