


On-load tap-changer type VUBBL, UBBL,
10 tap positions, linear switching.
Max effective No. of turns in pos 1.
The tap-changer is delivered set in pos 5.


Lindningskopplare typ VUBBL, UBBL,
10 lägen, linjär-koppling.
Max antal effektiva varv i läge 1.
Lindningskopplaren levereras inställd i läge 5.

| Pos Läge | H connects förbinder |
|-------------|----------------------------|
| 1 | 1 - 15 |
| 2 | 2 - 15 |
| 3 | 3 - 15 |
| 4 | 4 - 15 |
| 5 | 5 - 15 |
| 6 | 6 - 15 |
| 7 | 7 - 15 |
| 8 | 8 - 15 |
| 9 | 9 - 15 |
| 10 | 10 - 15 |

We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden.
© ABB '19



1) OUTPUT TERMINAL STRÖMAVTAGNING
*) FOR VUBB TYPE OF OLTC I VUBB UTFÖRANDE



1) Internal connections between the terminals 15 of the three phases are included in the star-point type. Dashed lines show in delivery not included leads belonging to cleats and leads.

H Main contact
Huvudkontakt

Inre förbindningar mellan uttag 15 i de tre faserna ingår i nollpunktsutförande. Streckade linjer visar i leveransen ej ingående ledare tillhörande anslutningsdonet.

| 2 | Output for VUBB type added. | DAAN | 20 | 14 |
|---------|-----------------------------|------|------|------|
| 1 | VUBBL added. | TL | 10 | 27 |
| Rev Ind | Revision | Appd | Year | Week |

| | |
|-------------------|-----------|
| Sheet | Cont |
| Year | Week |
| Dept | |
| Rev Ind | |
| Design checked by | |
| Drawn by | |
| Issued by | Year Week |
| COM/TKO | 97 32 |

| | | | |
|---|---|--|---------------------|
| Accepted by qual control R.Yngvesson | Accepted for prod by | Description (English) CONNECTION DIAGRAM | DATAORIGINAL |
| Design checked by B-O.Stenestam | Drawn by L.Bergman | Description (own language) KOPPLINGSSHEMA | File name 0387-6 |
| Drawing checked by M.Hedlund | Issued by Dept Year Week COM/TKO 97 32 | | Lang 1 |
| Asea Brown Boveri | | 5492 0387-6 | Rev Ind 2 |
| | | | Cont - |